

Computer AC Power Cable, NEMA 5-15P to C13 - 360-Degree Rotating Right-Angle 5-15P Plug, 10A, 125V, 18 AWG, 10 ft. (3 m), Black

MODEL NUMBER: P006-010-15RR



Connects your PC, printer or monitor to a surge protector, PDU or UPS with a NEMA 5-15R outlet.

Features

Desktop Computer Power Cord Connects PCs, Printers, Monitors and Other Equipment

This computer power cable is designed for home/office desktop computer applications. You can use it to connect a computer, monitor, printer, scanner or other device with a C14 power inlet to an AC wall outlet, surge protector, UPS system or PDU with a NEMA 5-15R outlet. The 10-foot (3-meter) length gives you some added flexibility in placing equipment away from the power outlet.

Rotating Flat Plug Allows an Easier Connection in Tight Spaces

The NEMA 5-15P input rotates 360 degrees, allowing you to connect it at any angle and making it easy to plug into a crowded wall outlet or surge protector without blocking adjacent outlets. The right-angle plug runs parallel to the outlet, so it can connect in a confined or hard-to-reach location, such as behind furniture, that leaves little space for cable bend.

Highlights

- Right-angle plug rotates 360° for easy connection in a confined location or crowded surge protector
- Recommended for powering computers, printers and other home/office peripherals
- 10 ft. length allows you extra flexibility in placing devices in relationship to AC outlet
- Ideal replacement for a worn-out or missing NEMA 5-15P to C13 power cable

Package Includes

P006-010-15RR NEMA 5-15P to C13 Computer Power Cable, 10 ft. (3 m), Black

Specifications

| OVERVIEW | |
|-----------------------------|------------------|
| UPC Code | 037332298300 |
| Device Compatibility | Computer; Laptop |
| Country/Region | North America |
| INPUT | |
| Maximum Input Amps | 10 |
| Voltage Compatibility (VAC) | 125 |
| CONNECTIONS | |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|--------------------------------------|-----------------------------|
| Side A - Connector 1 | NEMA 5-15P - RIGHT ANGLE |
| Side B - Connector 1 | IEC-320-C13 |
| PHYSICAL | |
| Plug Color | Black |
| Cable Jacket Color | Black |
| Cable Jacket Material | PVC |
| Cable Jacket Rating | SJT |
| Power Cord Jacket Type | SJT |
| Cable Outer Diameter (OD) | 7.7mm |
| Number of Conductors | 3 |
| Wire Gauge (AWG) | 18 |
| Wire Gauge (OD - mm ²) | 1.02 |
| Cable Length (ft.) | 10 |
| Cable Length (m) | 3.05 |
| Shipping Dimensions (hwd / in.) | 12.52 x 5.04 x 0.50 |
| Shipping Dimensions (hwd / cm) | 31.80 x 12.80 x 1.27 |
| Shipping Weight (lbs.) | 0.76 |
| Shipping Weight (kg) | 0.34 |
| Unit Dimensions (hwd / in.) | 12.520 x 5.040 x 0.500 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 23° to 158°F (-5° to 70°C) |
| Storage Temperature Range | 14° to 140°F (-10° to 60°C) |
| Operating Humidity Range | 35% to 85% RH |
| Storage Humidity Range | 35% to 85% RH |
| FEATURES & SPECIFICATIONS | |
| Antibacterial | No |
| Angled Plug | Yes |
| High Voltage | No |
| Locking Plug | No |
| Coiled Power Cord | No |
| P-Lock Power Cord | No |
| Locking Power Cord | No |
| STANDARDS & COMPLIANCE | |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|-------------------------------------|-------------------------------------|
| Product Certifications | CSA (Canada); UL Listed; cUL Listed |
| Product Compliance | WEEE |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.