

## Desktop Computer AC Power Cable, NEMA 5-15P to C13 - 10A, 125V, 18 AWG, 25 ft. (7.62 m), Black

MODEL NUMBER: P006-025



Computer power cable allows you to connect your PC, printer or monitor into a surge protector, PDU or UPS with a NEMA 5-15R outlet.

### Features

**Desktop Computer Power Cord Connects PCs, Printers, Monitors and Other Equipment** This computer power supply cable is designed for home/office desktop computer applications. You can use it to connect a computer, monitor, printer, scanner or other device with a C14 power inlet to an AC wall outlet, surge protector, UPS system or PDU. The 25-ft. (7.62 m) length allows you great flexibility in placing equipment with respect to the power outlet.

## Specifications

OVERVIEW	
UPC Code	037332180568
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	125
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC

### Highlights

- Recommended for powering computers, printers and other home/office peripherals
- 25-ft. (7.62 m) length allows great flexibility in placing devices in relationship to AC outlet
- NEMA 5-15P to C13 extension cord is ideal replacement for worn-out or missing cable

### Applications

- Connect devices like computers, printers and monitors to a PDU up to 25-ft. (7.62 m) away in your workstation
- Extend an existing power connection up to 25-ft. (7.62 m) to more easily place a device or reach a power source
- Provide a high-quality replacement for a worn-out or missing power cord

### Package Includes

- P006-025 NEMA 5-15P to C13 Computer Power Cable, 25-ft. (7.62 m), Black

Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.8mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm <sup>2</sup> )	0.82
Cable Length (ft.)	25
Cable Length (m)	7.62
Shipping Dimensions (hwd / in.)	14.17 x 11.81 x 0.50
Shipping Dimensions (hwd / cm)	35.99 x 30.00 x 1.27
Shipping Weight (lbs.)	1.59
Shipping Weight (kg)	0.72
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Storage Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Relative Humidity	10 - 85% RH
<b>CONNECTIONS</b>	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C13
<b>FEATURES &amp; SPECIFICATIONS</b>	
High Voltage	No
Locking Plug	No
Antibacterial	No
Angled Plug	No
Coiled Power Cord	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.