

Not for use in European Markets

Computer Power Cord, NEMA 5-15P to Locking C13 - 10A, 125V, 18 AWG, 6 ft. (1.83 m)

MODEL NUMBER: P006-L06



NEMA 5-15P to C13 power cable ensures a secure connection for all your equipment. Locking C13 connector prevents accidental disconnection.

Features

NEMA 5-15P to C13 Power Cable Connects Computers, Printers, Servers and Other Equipment This NEMA 5-15P to C13 power cable is designed for applications that do not require a heavy-duty cable. This UL-listed 5-15P to C13 power cord can be used to power a computer, printer or monitor or attach a server or drive to a UPS system or PDU.

Locking C13 Connector Helps Prevent Accidental Disconnection and Expensive Downtime Having a cable come loose accidentally can mean the loss of power and costly downtime. The P006-L06's locking C13 connector protects your critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

Lifetime Limited Warranty The P006-L06 is backed by a lifetime limited warranty, ensuring reliability and performance.

Specifications

OVERVIEW	
UPC Code	037332218278
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	10

Highlights

- Recommended for connecting power to computers, servers and other peripherals
- Adds 6-ft. (1.83 m) to your existing power connection to provide more flexibility in placing devices
- NEMA 5-15P to C13 cord is ideal replacement for worn-out or missing cable
- Locking C13 connector maintains secure link to avoid loss of power and costly downtime

Applications

- Connect devices like computers, servers and monitors to a PDU up to 6-ft. (1.83 m) away
- Prevent accidental disconnection with the C13 locking connector
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P006-L06 NEMA 5-15P to C13 Computer Power Cord, Locking C13 Connector - 10A, 125V, 18 AWG, 6-ft. (1.83 m)



Voltage Compatibility (VAC)	125
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.7mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.82
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	1.00 x 7.00 x 10.00
Shipping Dimensions (hwd / cm)	2.54 x 17.78 x 25.40
Shipping Weight (lbs.)	0.50
Shipping Weight (kg)	0.23
ENVIRONMENTAL	
Operating Temperature Range	-4 to 221 F (-20 to 105 C)
Storage Temperature Range	-4 to 221 F (-20 to 105 C)
Operating Humidity Range	0-65% RH
Storage Humidity Range	0-65% RH
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C13 - LOCKING
FEATURES & SPECIFICATIONS	
High Voltage	No
Locking Plug	Yes
Angled Plug	No
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); cUL Listed; UL Listed
Product Compliance	RoHS; REACH



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>