

**Important Note**

This product is not available in the European Union. If you live in one of these countries, please contact us for further assistance.

**Computer Power Cord, NEMA 5-15P to Locking C13 - 10A, 125V, 18 AWG, 10 ft. (3.05 m)**

MODEL NUMBER: P006-L10



NEMA 5-15P to C13 power cable ensures a secure connection for all your equipment. Locking C13 connector prevents accidental disconnection.

**Features**

**NEMA 5-15P to C13 Power Cable Connects Computers, Printers, Servers and Other Equipment** This NEMA 5-15P to C13 power cable is designed for applications that do not require a heavy-duty cable. This UL-listed 5-15P to C13 power cord can be used to power a computer, printer or monitor or attach a server or drive to a UPS system or PDU.

**Locking C13 Connector Helps Prevent Accidental Disconnection and Expensive Downtime** Having a cable come loose accidentally can mean the loss of power and costly downtime. The P006-L10's locking C13 connector protects your critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

**Lifetime Limited Warranty** The P006-L10 is backed by a lifetime limited warranty, ensuring reliability and performance.

**Specifications**

OVERVIEW	
UPC Code	037332218285
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America

**Highlights**

- Recommended for connecting power to computers, servers and other peripherals
- Adds 10-ft. (3.05 m) to your existing power connection to provide more flexibility in placing devices
- NEMA 5-15P to C13 cord is ideal replacement for worn-out or missing cable
- Locking C13 connector maintains secure link to avoid loss of power and costly downtime

**Applications**

- Connect devices like computers, servers and monitors to a PDU up to 10 ft. away
- Prevent accidental disconnection with the C13 locking connector
- Provide a high-quality replacement for a worn-out or missing power cord

**Package Includes**

- P006-L10 NEMA 5-15P to C13 Computer Power Cord, Locking C13 Connector - 10A, 125V, 18 AWG, 10 ft.



Powering Business Worldwide

TRIPP LITE  
SERIES

INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	125
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C13 - LOCKING
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.7mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm <sup>2</sup> )	0.82
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	12.80 x 9.25 x 0.50
Shipping Dimensions (hwd / cm)	32.51 x 23.50 x 1.27
Shipping Weight (lbs.)	0.70
Shipping Weight (kg)	0.32
ENVIRONMENTAL	
Operating Temperature Range	-4° to 221°F (-20° to 105°C)
Storage Temperature Range	-4° to 221°F (-20° to 105°C)
Operating Humidity Range	0% to 65% RH
Storage Humidity Range	0% to 65% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	Yes
Coiled Power Cord	No



Powering Business Worldwide

TRIPP LITE  
SERIES

Locking Power Cord	Yes
P-Lock Power Cord	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	CSA (Canada); cUL Listed; UL Listed
Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.