



# Desktop Computer Power Cable, NEMA 5-15P to C13 - 10A, 125V, 18 AWG, 12 ft. (3.66 m), Black

## MODEL NUMBER: P010-012







Computer power cable allows you to connect your PC, printer or monitor into a surge protector, PDU or UPS with a NEMA 5-15R outlet.

### Features

**Desktop Computer Power Cord Connects PCs, Printers, Monitors and Other Equipment**This computer power supply cable is designed for home/office desktop computer applications. You can use it to connect a computer, monitor, printer, scanner or other device with a C14 power inlet to an AC wall outlet, surge protector, UPS system or PDU. The 12-ft. (3.66 m) length allows you great flexibility in placing equipment with respect to the power outlet.

# **Specifications**

| OVERVIEW                    |   |
|-----------------------------|---|
| UPC Code                    | 037332013415                                      |
| Device Compatibility        | Computer; Monitor/HDTV; Printer; Server; UPS; PDU |
| Country/Region              | North America                                     |
| INPUT                       |   |
| Maximum Input Amps          | 10  |
| Voltage Compatibility (VAC) | 125   |
| CONNECTIONS                 |   |
| Side A - Connector 1        | NEMA 5-15P  |
| Side B - Connector 1        | IEC-320-C13                                       |
| PHYSICAL                    |   |

### Highlights

- Recommended for powering computers, printers and other home/office peripherals
- 12-ft. (3.66 m) length allows great flexibility in placing devices in relationship to AC outlet
- Ideal replacement for a worn-out or missing NEMA 5-15P to C13 cable

### **Applications**

- Connect devices like computers, printers and monitors to a PDU up to 12-ft. (3.66 m) away in your workstation
- Extend an existing power connection up to 12-ft. (3.66 m) to more easily place a device or reach a power source
- Provide a high-quality replacement for a worn-out or missing power cord

#### **Package Includes**

 P010-012 NEMA 5-15P to C13 Computer Power Cable, 12-ft. (3.66 m), Black





| RoHS                        |
|-----------------------------|
| cUL Listed; UL Listed       |
|                             |
| No                          |
|                             |
| 10% to 65% RH               |
| 10% to 65% RH               |
| -4° to 140°F (-20° to 60°C) |
| -4° to 140°F (-20° to 60°C) |
|                             |
|                             |
| 0.39                        |
| 0.86                        |
| 25.40 x 18.03 x 1.27        |
| 10.00 x 7.10 x 0.50         |
| 3.66                        |
| 12                          |
| 0.82                        |
| 18                          |
| 3                           |
| 6.3mm                       |
| SVT                         |
| VW-1                        |
| PVC                         |
| Black                       |
|                             |





1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.