

2-Slot Non-Polarized Laptop Notebook Power Cord, 1-15P to C7 - 10A, 120V, 18 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: P012-006



Laptop power cord connects your notebook, VCR, DVD player or other device that uses a non-polarized 2-prong cord to an AC outlet.

Features

2-Slot Power Cord Connects Laptops, VCRs, DVD Players and Other Equipment This 2-slot non-polarized power cord is designed for connecting a notebook computer, VCR, DVD player or other device that uses a non-polarized 2-prong cord to an AC wall outlet, surge protector, UPS system or PDU. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

Specifications

OVERVIEW	
UPC Code	037332013422
Device Compatibility	Laptop; DVR; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	125
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC

Highlights

- Recommended for powering notebook computers and other home/office peripherals
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for a worn-out or missing laptop power cable

Applications

- Connect a laptop or DVD player to a PDU up to 6-ft. (1.83 m) away in your workstation or home theater setup
- Extend an existing power connection up to 6-ft. (1.83 m) to more easily place a device or reach a power source
- Provide a high-quality replacement for a worn-out or missing laptop power cord

Package Includes

- P012-006 2-Slot Non-Polarized Laptop Notebook Power Cord, 1-15P to C7 - 6-ft. (1.83 m), Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Jacket Rating	VW-1
Power Cord Jacket Type	SPT-2
Cable Outer Diameter (OD)	6.9mm
Number of Conductors	2
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.82
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / cm)	0.25 x 31.24 x 20.57
Shipping Dimensions (hwd / in.)	0.10 x 12.30 x 8.10
Shipping Weight (kg)	0.10
Shipping Weight (lbs.)	0.21
ENVIRONMENTAL	
Operating Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Storage Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Operating Humidity Range	10 TO 65% RH
Storage Humidity Range	10 TO 65% RH
CONNECTIONS	
Side A - Connector 1	NEMA 1-15P (NON-POLARIZED)
Side B - Connector 1	IEC-320-C7 (NON-POLARIZED)
FEATURES & SPECIFICATIONS	
High Voltage	No
Locking Plug	No
Angled Plug	No
STANDARDS & COMPLIANCE	
Certifications	UL/Cul
Approvals	UL/CSA
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

<https://www.tripplite.com/products/product-certification-agencies>