

## Power Cord C14 to C15 - Heavy-Duty, 15A, 250V, 14 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: P018-006



### Highlights

- 6-ft. heavy-duty power cord, C14-to-C15
- 100-250V, 15A, 14AWG, SJT
- UL Listed

### Package Includes

- 6-ft. C14 to C15 Power Cord

Connect network hardware with C15 power connections such as servers to PDUs and UPS systems with C14 type inputs.

### Features

- Heavy-duty power cord supports up to 250V
- Flexible 14AWG wire for easy routing
- Use with Cisco, HP and other hardware that uses C15 type power connections
- UL Listed

## Specifications

OVERVIEW	
UPC Code	037332168443
Device Compatibility	Network Switch; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	15
Voltage Compatibility (VAC)	100-250
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC

Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	9.3mm
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm <sup>2</sup> )	2.08
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	1.00 x 7.00 x 11.00
Shipping Dimensions (hwd / cm)	2.54 x 17.78 x 27.94
Shipping Weight (lbs.)	0.76
Shipping Weight (kg)	0.34
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Storage Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Operating Humidity Range	10 TO 65% RH
Storage Humidity Range	10 TO 65% RH
<b>CONNECTIONS</b>	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C15
<b>FEATURES &amp; SPECIFICATIONS</b>	
High Voltage	Yes
Locking Plug	No
Antibacterial	No
Angled Plug	No
Coiled Power Cord	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.