

## Power Cord, NEMA 5-15P to Right-Angle C15 - Heavy-Duty, 15A, 125V, 14 AWG, 8 ft. (2.43 m), Black

MODEL NUMBER: P019-008-C15RA



C15 right-angle power cable connects a PoE network switch or other device with a C16 power inlet in tight spaces or awkward angles.

### Features

**IEC C15 Power Cord for Network Devices That Require a Heavy-Gauge Connection** This IEC C15 power cable features 14 AWG wire suitable for high power connections, making it reliable for large server applications that require a higher-rated, heavier-gauge cable. The C15 connector is designed for higher-temperature devices, such as electric kettles, PoE (Power over Ethernet) switches with high-wattage power supplies, and similar network components. This cord can also replace or upgrade the standard power cord provided by the device's manufacturer. The 8-ft. (2.43 m) length allows you flexibility in placing equipment with respect to the power outlet.

**Right-Angle C15 Plug Makes Connecting in Tight Spaces Easier** The C15 right-angle power cable is easier to install in confined spaces, such as the back of a rack enclosure cabinet. When plugged in, the right-angled C15 plug guides the cable parallel to your peripheral, allowing you to push the device up against a wall or hide it behind a desk to maximize space.

### Highlights

- Right-angle C15 plug allows easier connection in confined or hard-to-reach spaces
- Recommended for powering PoE switches with high-wattage power supplies
- 8-ft. (2.43 m) length allows flexibility in placing devices in relationship to AC outlet
- NEMA 5-15P to C15 cable replaces or upgrades original manufacturer's power cord
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

### Applications

- Connect devices like high-wattage PoE switches to a PDU up to 8-ft. (2.43 m) away in your data center
- Extend an existing power connection up to 8-ft. (2.43 m) to more easily place a device or reach a power source
- Update or replace the standard power cord provided by a device's original manufacturer
- Power a device located in a hard-to-access area behind a desk or flush against a wall

### Package Includes

- P019-008-C15RA 5-15P to Right-Angle C15 Power Cord, 8-ft. (2.43 m), Black

## Specifications



<b>OVERVIEW</b>	
UPC Code	037332202413
Device Compatibility	Computer; Server; Network Switch; UPS; PDU
Country/Region	North America
<b>INPUT</b>	
Maximum Input Amps	15
Cable Length (ft.)	8
Cable Length (m)	2.4
Cable Length (in.)	96
Voltage Compatibility (VAC)	125
<b>PHYSICAL</b>	
Wire Gauge (AWG)	14
Wire Gauge (OD - mm <sup>2</sup> )	2.08
Color	Black
Number of Conductors	3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	1.27 x 29.97 x 35.56
Shipping Dimensions (hwd / in.)	0.50 x 11.80 x 14.00
Shipping Weight (kg)	0.45
Shipping Weight (lbs.)	1.00
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Storage Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Operating Humidity Range	10-85% RH
Storage Humidity Range	10-85% RH
<b>CONNECTIONS</b>	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C15 – RIGHT ANGLE
<b>SPECIAL FEATURES</b>	
High Voltage	No
Locking Plug	No



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>