

Power Extension Cord, NEMA 5-15P to NEMA 5-15R - 10A, 120V, 18 AWG, 12 ft. (3.66 m), Black

MODEL NUMBER: P022-012



12 ft. extension cord connects two devices with 5-15P/5-15R power connectors or extends your existing power connection.

Features

12-ft. (3.66 m) Extension Cord Connects Computers, Printers, Servers and Other Equipment This power extension cable is designed for small data center or office workstation applications that do not require a heavy-gauge connection. With a NEMA 5-15P plug on one end and a NEMA 5-15R receptacle on the other, this cord can be used to power a computer, printer or monitor; attach a rack server to a UPS system or PDU; or extend an existing connection up to 12-ft. (3.66 m). The 12-ft. (3.66 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Highlights

- Recommended for powering computers, monitors and other essential peripherals
- Adds 12-ft. (3.66 m) to your existing connection to provide more flexibility in placing devices
- Ideal replacement for worn-out or missing 12-ft. (3.66 m) extension cord

Applications

- Connect devices like computers, servers and monitors to a PDU up to 12-ft. (3.66 m) away in your data center
- Extend an existing power connection up to 12-ft. (3.66 m) to more easily place a device or reach a power source away from your workstation
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P022-012 Power Extension Cord, NEMA 5-15P to NEMA 5-15R, 12-ft. (3.66 m), Black

Specifications

OVERVIEW	
UPC Code	037332205971
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	125
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	NEMA 5-15R
PHYSICAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.7mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.82
Cable Length (ft.)	12
Cable Length (m)	3.66
Shipping Dimensions (hwd / in.)	14.17 x 11.80 x 0.50
Shipping Dimensions (hwd / cm)	35.99 x 29.97 x 1.27
Shipping Weight (lbs.)	0.79
Shipping Weight (kg)	0.36
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 80% RH
Storage Humidity Range	20% to 80% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.