

Power Extension Cord, NEMA 5-15P to NEMA 5-15R - 13A, 120V, 16 AWG, 12 ft. (3.7 m), Black

MODEL NUMBER: P022-012-13A



13-amp extension cord connects two devices with 5-15P/5-15R power connectors or extends your existing power connection.

Features

12-Foot Extension Cord Connects Monitors, Printers, Servers and Other Equipment

This power extension cable is designed for small data center or office workstation applications that do not require a heavy-gauge connection. With a NEMA 5-15P plug on one end and a NEMA 5-15R receptacle on the other, this UL listed (UL 817) cord can be used to power a printer or monitor, attach a rack server to a PDU or extend an existing connection up to 12 feet (3.7 meters). The 12-foot length allows you more flexibility in placing equipment with respect to the power outlet.

Highlights

- Recommended for powering printers, monitors and other essential peripherals
- Ideal for home/office applications, small server rooms and data centers
- Adds 12 ft. to your existing connection to provide more flexibility in placing devices
- UL listed cable is ideal replacement for worn-out or missing extension cord

Package Includes

P022-012-13A Power Extension Cord, NEMA 5-15P to NEMA 5-15R, 12 ft. (3.7 m), Black

Specifications

OVERVIEW	
UPC Code	037332275226
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	13
Voltage Compatibility (VAC)	125
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	NEMA 5-15R
PHYSICAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	8.3mm
Number of Conductors	3
Wire Gauge (AWG)	16
Wire Gauge (OD - mm ²)	1.31
Cable Length (ft.)	12
Cable Length (m)	3.66
Shipping Dimensions (hwd / in.)	14.17 x 11.80 x 0.50
Shipping Dimensions (hwd / cm)	35.99 x 29.97 x 1.27
Shipping Weight (lbs.)	0.88
Shipping Weight (kg)	0.40
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% TO 80% RH, NON-CONDENSING
Storage Humidity Range	20% to 80% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 817; UL Listed; cUL Listed
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.