

Power Extension Cord, NEMA 5-15P to NEMA 5-15R - 13A, 120V, 16 AWG, 12 ft. (3.7 m), Black

MODEL NUMBER: P022-012-13A



13-amp extension cord connects two devices with 5-15P/5-15R power connectors or extends your existing power connection.

Features

12-Foot Extension Cord Connects Monitors, Printers, Servers and Other Equipment

This power extension cable is designed for small data center or office workstation applications that do not require a heavy-gauge connection. With a NEMA 5-15P plug on one end and a NEMA 5-15R receptacle on the other, this UL listed (UL 817) cord can be used to power a printer or monitor, attach a rack server to a PDU or extend an existing connection up to 12 feet (3.7 meters). The 12-foot length allows you more flexibility in placing equipment with respect to the power outlet.

Specifications

| OVERVIEW | |
|-----------------------------|---|
| UPC Code | 037332275226 |
| Device Compatibility | Computer; Monitor/HDTV; Printer; Server; UPS; PDU |
| Country/Region | North America |
| INPUT | |
| Maximum Input Amps | 13 |
| Voltage Compatibility (VAC) | 125 |
| PHYSICAL | |
| Plug Color | Black |
| Cable Jacket Color | Black |
| Cable Jacket Material | PVC |

Highlights

- Recommended for powering printers, monitors and other essential peripherals
- Ideal for home/office applications, small server rooms and data centers
- Adds 12 ft. to your existing connection to provide more flexibility in placing devices
- UL listed cable is ideal replacement for worn-out or missing extension cord

Package Includes

P022-012-13A Power Extension Cord, NEMA 5-15P to NEMA 5-15R, 12 ft. (3.7 m), Black

| | |
|--------------------------------------|-------------------------------|
| Cable Jacket Rating | FT2 |
| Power Cord Jacket Type | SJT |
| Cable Outer Diameter (OD) | 8.3mm |
| Number of Conductors | 3 |
| Wire Gauge (AWG) | 16 |
| Wire Gauge (OD - mm ²) | 1.31 |
| Cable Length (ft.) | 12 |
| Cable Length (m) | 3.66 |
| Shipping Dimensions (hwd / in.) | 14.17 x 11.80 x 0.50 |
| Shipping Dimensions (hwd / cm) | 35.99 x 29.97 x 1.27 |
| Shipping Weight (lbs.) | 0.88 |
| Shipping Weight (kg) | 0.40 |
| ENVIRONMENTAL | |
| Operating Temperature Range | -4° to 140°F (-20° to 60°C) |
| Storage Temperature Range | -4° to 140°F (-20° to 60°C) |
| Operating Humidity Range | 20% TO 80% RH, NON-CONDENSING |
| Storage Humidity Range | 20% to 80% RH, Non-Condensing |
| CONNECTIONS | |
| Side A - Connector 1 | NEMA 5-15P |
| Side B - Connector 1 | NEMA 5-15R |
| FEATURES & SPECIFICATIONS | |
| Antibacterial | No |
| Angled Plug | No |
| High Voltage | No |
| Locking Plug | No |
| Coiled Power Cord | No |
| STANDARDS & COMPLIANCE | |
| Product Certifications | UL 817; UL Listed; cUL Listed |
| Product Compliance | RoHS; REACH |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.