

# Power Extension Cord, Right-Angle NEMA 5-15P to NEMA 5-15R - 10A, 120V, 18 AWG, 15 ft. (4.57 m), Black

MODEL NUMBER: P022-015-15D



15 ft. extension cord connects two devices with 5-15P/5-15R power connectors or extends your existing power connection.

## Features

**15-ft. (4.57 m) Extension Cord Connects Computers, Printers, Servers and Other Equipment** This power extension cable is designed for small data center or office workstation applications that do not require a heavy-gauge connection. With a right-angle NEMA 5-15P plug on one end and a NEMA 5-15R receptacle on the other, this cord can be used to power a computer, printer or monitor; attach a rack server to a UPS system or PDU; or extend an existing connection up to 15-ft. (4.57 m). The 15-ft. (4.57 m) length allows you great flexibility in placing equipment with respect to the power outlet.

**Right-Angle Plug Makes Connecting in Tight Spaces Easier** The space-saving right-angle NEMA 5-15P connector is easy to install in confined spaces, such as behind your computer desk or workstation. The right-angle construction also relieves strain on the cable and connector and prevents the cable from bending awkwardly.

## Specifications

OVERVIEW	
UPC Code	037332243843
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	125
CONNECTIONS	

## Highlights

- Recommended for powering computers, monitors and other essential peripherals
- Ideal for home/office applications, small server rooms and data centers
- Right-angle plug allows easier connection in confined or hard-to-reach spaces
- Adds 15-ft. (4.57 m) to your existing connection to provide more flexibility in placing devices
- Ideal replacement for worn-out or missing 15-ft. (4.57 m) extension cord

## Applications

- Connect devices like computers, servers and monitors to a PDU up to 15-ft. (4.57 m) away in your data center
- Extend an existing power connection up to 15-ft. (4.57 m) to more easily place a device or reach a power source away from your workstation
- Provide a high-quality replacement for a worn-out or missing power cord

## Package Includes

- P022-015-15D Power Extension Cord, Right-Angle NEMA 5-15P to NEMA 5-15R, 15-ft. (4.57 m), Black



Powering Business Worldwide

TRIPP LITE  
SERIES

Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	NEMA 5-15R
<b>PHYSICAL</b>	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.7mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm <sup>2</sup> )	0.82
Cable Length (ft.)	15
Cable Length (m)	4.57
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 80% RH
Storage Humidity Range	20% to 80% RH
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Angled Plug	Yes
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.