

## Power Extension Cord, NEMA 5-15P to NEMA 5-15R - 10A, 120V, 18 AWG, 25 ft. (7.62 m), Black

MODEL NUMBER: P022-025



25 ft. extension cord connects two devices with 5-15P/5-15R power connectors or extends your existing power connection.

### Features

**25-ft. (7.62 m) Extension Cord Connects Computers, Printers, Servers and Other Equipment** This power extension cable is designed for small data center or office workstation applications that do not require a heavy-gauge connection. With a NEMA 5-15P plug on one end and a NEMA 5-15R receptacle on the other, this cord can be used to power a computer, printer or monitor; attach a rack server to a UPS system or PDU; or extend an existing connection up to 25-ft. (7.62 m). The 25-ft. (7.62 m) length allows you great flexibility in placing equipment with respect to the power outlet.

## Specifications

OVERVIEW	
UPC Code	037332164872
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	125
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC

### Highlights

- Recommended for powering computers, monitors and other essential peripherals
- Adds 25-ft. (7.62 m) to your existing connection to provide more flexibility in placing devices
- Ideal replacement for worn-out or missing 25-ft. (7.62 m) extension cord

### Applications

- Connect devices like computers, servers and monitors to a PDU up to 25-ft. (7.62 m) away in your data center
- Extend an existing power connection up to 25-ft. (7.62 m) to more easily place a device or reach a power source away from your workstation
- Provide a high-quality replacement for a worn-out or missing power cord

### Package Includes

- P022-025 Power Extension Cord, NEMA 5-15P to NEMA 5-15R, 25-ft. (7.62 m), Black

Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.8mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm <sup>2</sup> )	0.82
Cable Length (ft.)	25
Cable Length (m)	7.62
Shipping Dimensions (hwd / in.)	1.50 x 11.00 x 15.00
Shipping Dimensions (hwd / cm)	3.81 x 27.94 x 38.10
Shipping Weight (lbs.)	1.70
Shipping Weight (kg)	0.77
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	10% to 65% RH
Storage Humidity Range	10% to 65% RH
<b>CONNECTIONS</b>	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	NEMA 5-15R
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.