

## Power Extension Cord, Right-Angle 5-15P to 5-15R, 13A, 120V, 16 AWG, 3 ft. (0.91 m), Black

MODEL NUMBER: P024-003-13A15D



3 ft. extension cord with a Right Angle 5-15P and 5-15R connectors connects bulky power transformers without blocking adjacent outlets on your PDU.

### Features

**3-ft. (0.91 m) Extension Cord Connects PCs, Printers, Monitors and Other Equipment** This cord is recommended for home/office desktop computer applications, home theater setups or other applications where multiple devices are plugged into a surge protector, PDU or UPS system. It allows you to connect bulky power adapters to a NEMA 5-15R outlet without blocking adjacent outlets. It's also an excellent replacement for a lost or worn-out extension cord. The three-foot length helps reduce cable clutter and minimize the risk of tripping.

**Right-Angle Plug Makes Connecting in Tight Spaces Easier** The space-saving right-angle NEMA 5-15P connector is easy to install in confined spaces, such as behind your computer desk or workstation. The right-angle construction also relieves strain on the cable and connector and prevents the cable from bending awkwardly.

### Highlights

- Recommended for powering computers, printers and other home/office peripherals
- 3-ft. (0.91 m) length allows flexibility in placing devices, while avoiding cable clutter
- Ideal replacement for worn-out or missing 3-ft. (0.91 m) extension cord
- Right Angle 5-15P connector is ideal for tight spaces

### Applications

- Connect devices like computers, servers and monitors to a PDU in your data center
- Extend an existing power connection up to 3-ft. (0.91 m) to more easily place a device or reach a power source in a rack
- Provide a high-quality replacement for a worn-out or missing power cord

### Package Includes

- P024-003-13A15D 3-ft. (0.91 m) Extension Cord, Right-Angle NEMA 5-15P to NEMA 5-15R, Black

## Specifications

OVERVIEW	
UPC Code	037332243836
Country/Region	North America
INPUT	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Maximum Input Amps	13
Cable Length (ft.)	3
Cable Length (m)	0.9
Cable Length (in.)	36
Voltage Compatibility (VAC)	120
<b>PHYSICAL</b>	
Color	Black
Number of Conductors	3
Power Cord Jacket Type	SJT
Wire Gauge (AWG)	16
Wire Gauge (OD - mm <sup>2</sup> )	1.31
<b>CONNECTIONS</b>	
Side A - Connector 1	NEMA 5-15P - RIGHT ANGLE
Side B - Connector 1	NEMA 5-15R
<b>SPECIAL FEATURES</b>	
High Voltage	No
Locking Plug	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>