

Power Extension Cord, Right-Angle NEMA 5-15P to NEMA 5-15R - Heavy-Duty, 15A, 120V, 14 AWG, 10 ft. (3.05 m), Black

MODEL NUMBER: P024-010-15D



10 ft. extension cord with 5-15R and right-angle 5-15P connectors connects your server to a PDU, UPS, surge protector or wall outlet.

Features

Heavy-Duty Extension Cable for Network Devices That Require a Heavy-Gauge Connection This 10-ft. (3.05 m) extension cord features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. It can be used to connect a computer, server or other device with a NEMA 5-15P plug to a PDU, UPS system, surge protector or wall outlet with a NEMA 5-15R outlet. The 10-ft. (3.05 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Right-Angle Plug Makes Connecting in Tight Spaces Easier The space-saving right-angle NEMA 5-15P connector is easy to install in confined spaces, such as behind your computer desk or workstation. The right-angle construction also relieves strain on the cable and connector and prevents the cable from bending awkwardly.

Specifications

OVERVIEW	
UPC Code	037332243881
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	15
Voltage Compatibility (VAC)	125
CONNECTIONS	

Highlights

- Recommended for powering computers, servers and other home/office peripherals
- Right-angle plug allows easier connection in confined or hard-to-reach spaces
- Heavy-duty cord replaces or upgrades standard power cord provided by manufacturer
- 10-ft. (3.05 m) length allows great flexibility in placing devices in relationship to AC outlet
- Ideal replacement for worn-out or missing 10-ft. (3.05 m) extension cord

Applications

- Connect devices like computers, servers and monitors to a PDU in your data center
- Extend an existing power connection up to 10-ft. (3.05 m) to more easily place a device or reach a power source in a rack
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P024-010-15D Heavy-Duty 10-ft. (3.05 m) Extension Cord, Right-Angle NEMA 5-15P to NEMA 5-15R, Black



Powering Business Worldwide

TRIPP LITE
SERIES

Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	NEMA 5-15R
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	9.2mm
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm ²)	2.08
Cable Length (ft.)	10
Cable Length (m)	3.05
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 80% RH
Storage Humidity Range	20% to 80% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	Yes
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.