

Power Extension Cord, NEMA 5-15P to NEMA 5-15R - Heavy-Duty, 15A, 120V, 14 AWG, 25 ft. (7.62 m), Black

MODEL NUMBER: P024-025



25 ft. extension cord connects your computer or other device with a NEMA 5-15P plug to a PDU or UPS with a NEMA 5-15R outlet.

Features

Heavy-Duty Extension Cable for Network Devices That Require a Heavy-Gauge Connection This 25-ft. (7.62 m) extension cord features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. It can be used to connect a computer, monitor, printer or other device with a NEMA 5-15P plug to a wall outlet, PDU, surge protector or UPS system with a NEMA 5-15R outlet. The 25-ft. (7.62 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Specifications

OVERVIEW	
UPC Code	037332197160
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	15
Voltage Compatibility (VAC)	125
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black

Highlights

- Recommended for powering computers, printers and other home/office peripherals
- 25-ft. (7.62 m) length allows great flexibility in placing devices in relationship to AC outlet
- Ideal replacement for worn-out or missing 25-ft. (7.62 m) extension cord

Applications

- Connect devices like computers, servers and monitors to a PDU in your data center
- Extend an existing power connection up to 25-ft. (7.62 m) to more easily place a device or reach a power source in a rack
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P024-025 25-ft. (7.62 m) Extension Cord, NEMA 5-15P to NEMA 5-15R, Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	9.3mm
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm ²)	2.08
Cable Length (ft.)	25
Cable Length (m)	7.62
Cable Length (cm)	762.00
Shipping Dimensions (hwd / cm)	35.99 x 29.97 x 1.27
Shipping Dimensions (hwd / in.)	14.17 x 11.80 x 0.50
Shipping Weight (kg)	1.12
Shipping Weight (lbs.)	2.46
ENVIRONMENTAL	
Operating Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Storage Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Operating Humidity Range	10 TO 65% RH
Storage Humidity Range	10 TO 65% RH
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	NEMA 5-15R
FEATURES & SPECIFICATIONS	
High Voltage	No
Locking Plug	No
Angled Plug	No
STANDARDS & COMPLIANCE	
Certifications	UL/Cul
Approvals	UL/CSA
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>