

## Extension Cord Y Splitter, NEMA 5-15P to 2x NEMA 5-15R - 13A, 120V, 16 AWG, 18-in. (45.72 cm), Black

MODEL NUMBER: P024-18N-13A-2R



Extension cord splitter allows 2 devices with NEMA 5-15P plugs to share one AC power input cord and one NEMA 5-15R outlet.

### Features

**Y-Style Power Cord Splitter Connects 2 Devices with NEMA 5-15P Plugs to One AC Outlet** This extension cable splitter allows two devices with NEMA 5-15P plugs to share one AC input cord and one NEMA 5-15R outlet. By connecting two devices to one outlet, the extension cord splitter frees up space in a PDU, UPS system or surge protector and helps reduce cable clutter. You can also free up valuable PDU space by connecting bulky power adapters to this splitter, preventing the adapters from blocking adjacent outlets.

**Dual Cable Powers a Wide Variety of Essential Electronics** With this splitter, a single NEMA 5-15R outlet can power two devices, such as computers, monitors, printers, instrument amplifiers and other equipment compatible with a 5-15P connector. Ideal for areas where AC outlets are limited, such as rack cabinets, this dual power cable is compatible with Tripp Lite power and extension cords.

### Highlights

- Connects 2 devices to one AC outlet to save space and reduce cable clutter
- Recommended for powering dual computers, monitors or other compatible peripherals
- Ideal replacement for worn-out or missing extension cord Y splitter
- NEMA 5-15P plug connects to AC power; 5-15R ends connect to devices' power cords

### Applications

- Connect 2 devices like computers, monitors, scanners and printers to one power outlet up to 1.5 ft. away in your home office, work space or dorm room
- Cut cable clutter by powering both monitors in a dual-monitor display mount with a single cord
- Save space in a 0U vertical rack-mount PDU by plugging two rack devices into one outlet

### Package Includes

- P024-18N-13A-2R Extension Cord Y Splitter, 5-15P to 2x 5-15R, 1.5 ft., Black

## Specifications

OVERVIEW	
UPC Code	037332180636
Country/Region	North America



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

<b>INPUT</b>	
Maximum Input Amps	13
Cable Length (ft.)	1.5
Cable Length (m)	0.5
Voltage Compatibility (VAC)	120
<b>PHYSICAL</b>	
Color	Black
Number of Conductors	3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	25.40 x 18.03 x 0.25
Shipping Dimensions (hwd / in.)	10.00 x 7.10 x 0.10
Shipping Weight (kg)	0.19
Shipping Weight (lbs.)	0.41
Wire Gauge (AWG)	16
Wire Gauge (OD - mm <sup>2</sup> )	1.31
<b>CONNECTIONS</b>	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	(2) NEMA 5-15R
<b>SPECIAL FEATURES</b>	
High Voltage	No
Locking Plug	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>