

# Desktop Computer Power Cord, NEMA 5-15P to C13, 5-Pack - 10A, 125V, 18 AWG, 2 ft. (0.61 m), Black

MODEL NUMBER: P030-002-5



Computer power cables connect your server, switch, router and other devices to a surge protector, PDU or UPS system with 5-15R outlets.

## Features

**Desktop Computer Power Cords Connect Essential Network Equipment** This computer power supply cable is designed for keeping mission-critical network equipment operating at all times. You can use it to connect a computer, monitor, printer, server, switch, router or other device with a C14 power inlet to an AC wall outlet, surge protector, UPS system or PDU. The 2-ft. (0.61 m) length helps reduce cable clutter and minimize the risk of tripping. Five power supply cables are included.

## Specifications

OVERVIEW	
UPC Code	037332143280
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; Network Switch; Router; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	125
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C13
PHYSICAL	

## Highlights

- Recommended for powering servers, switches, routers and other network devices
- 2-ft. (0.61 m) length allows flexibility in placing devices, while avoiding cable clutter
- Ideal replacements for worn-out or missing NEMA 5-15P to C13 power cables

## Applications

- Connect devices like servers, switches and routers to a PDU in your data center
- Extend existing power connections up to 2-ft. (0.61 m) to more easily place devices or reach a power source
- Provide high-quality replacements for worn-out or missing power cords

## Package Includes

- P030-002-5 Desktop Computer Power Cord, NEMA 5-15P to C13, 5-Pack, 2-ft. (0.61 m), Black



Powering Business Worldwide

TRIPP LITE  
SERIES

Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.7mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm <sup>2</sup> )	0.82
Cable Length (ft.)	2
Cable Length (m)	0.61
Shipping Dimensions (hwd / in.)	9.98 x 7.09 x 0.50
Shipping Dimensions (hwd / cm)	25.35 x 18.01 x 1.27
Shipping Weight (lbs.)	1.10
Shipping Weight (kg)	0.50
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 80% RH
Storage Humidity Range	20% to 80% RH
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.