

Splitter Cable, Heavy Duty, C20 to 2x C13 - 15A, 100-250V, 14 AWG, 2 ft., Black

MODEL NUMBER: P032-002-2C13



C20-to-C13 splitter allows 2 devices with C14 inlets to share one AC power input cord and one C19 outlet on a PDU or UPS system.

Features

Heavy-Duty Splitter Cable for Network Devices That Require a Heavy-Gauge Connection This C20-to-C13 splitter features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. It allows two devices with C14 power inlets to share one AC input cord and one C19 outlet. By connecting two devices to one outlet, the splitter frees up space in a PDU or surge protector and helps reduce cable clutter. The two-foot length helps reduce cable clutter and minimize the risk of tripping.

Dual IEC Cable Powers a Wide Variety of Essential Electronics With this splitter, a single C19 outlet can power two devices, such as computers, monitors, printers, instrument amplifiers and other equipment compatible with a C19 connector. Ideal for areas where AC outlets are limited, such as rack cabinets, this dual IEC cable is compatible with Tripp Lite power and extension cords.

Highlights

- Connects 2 devices to one AC outlet to save space and reduce cable clutter
- Recommended for powering dual computers, monitors or other compatible peripherals
- 2 ft. length allows flexibility in placing devices, while avoiding cable clutter
- Heavy-duty cord replaces or upgrades standard power cords provided by manufacturer
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

Applications

- Connect 2 devices like computers, monitors, scanners and printers to one power outlet up to 2 ft. away in your home office, work space or dorm room
- Cut cable clutter by powering both monitors in a dual-monitor display mount with a single cord
- Save space in a 0U vertical rack-mount PDU by plugging two rack devices into one outlet

Package Includes

- P032-002-2C13 C20 to C13 Splitter, 2 ft., Black

Specifications

OVERVIEW	
UPC Code	037332156495



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Country/Region	North America
INPUT	
Maximum Input Amps	15
Cable Length (ft.)	2
Cable Length (m)	0.6
Voltage Compatibility (VAC)	100-250
PHYSICAL	
Color	Black
Number of Conductors	3
Power Cord Jacket Type	SJTW
Shipping Dimensions (hwd / cm)	32.51 x 22.61 x 1.27
Shipping Dimensions (hwd / in.)	12.80 x 8.90 x 0.50
Shipping Weight (kg)	0.25
Shipping Weight (lbs.)	0.56
Wire Gauge (AWG)	14
Wire Gauge (OD - mm ²)	2.08
CONNECTIONS	
Side A - Connector 1	IEC-320-C20
Side B - Connector 1	(2) IEC-320-C13
SPECIAL FEATURES	
High Voltage	Yes
Locking Plug	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>