

C20 to C13 Power Cord for Computer - Heavy-Duty, 15A, 100-250V, 14 AWG, 7 ft. (2.13 m), Black

MODEL NUMBER: P032-007



C20-to-C13 adapter connects devices with C19/C14 power connectors or extends your existing power connection by 7 ft.

Features

Heavy-Duty Computer Power Cord for Devices That Require a Heavy-Gauge Connection This C20-to-C13 power cable features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This IEC C20-to-C13 cord can be used to connect a computer, server, monitor or drive to a UPS system or PDU or replace or upgrade the standard power cord provided by the device's manufacturer. The seven-foot length allows you flexibility in placing equipment with respect to the power outlet.

Specifications

OVERVIEW	
UPC Code	037332126313
Device Compatibility	Computer; Monitor/HDTV; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	15
Voltage Compatibility (VAC)	100-250
PHYSICAL	
Cable Jacket Color	Black
Cable Jacket Material	PVC

Highlights

- Recommended for powering computers, servers and other network devices
- 7-ft. (2.13 m) length allows flexibility in placing devices in relationship to AC outlet
- Heavy-duty C13-to-C20 cable replaces or upgrades standard cord provided by manufacturer
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

Applications

- Connect devices like computers, servers and monitors to a PDU up to 7-ft. (2.13 m) away in your data center
- Extend an existing power connection up to 7-ft. (2.13 m) to more easily place a device or reach a power source
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P032-007 C20 to C13 Power Cable for Computer, 7-ft. (2.13 m), Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Plug Color	Black
Power Cord Jacket Type	SJTW
Cable Jacket Rating	VW-1
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm ²)	2.08
Cable Length (ft.)	7
Cable Length (m)	2.1336
Shipping Dimensions (hwd / cm)	32.51 x 22.61 x 1.27
Shipping Dimensions (hwd / in.)	12.80 x 8.90 x 0.50
Shipping Weight (kg)	0.52
Shipping Weight (lbs.)	1.15
ENVIRONMENTAL	
Operating Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Storage Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Operating Humidity Range	10 TO 65% RH
Storage Humidity Range	10 TO 65% RH
CONNECTIONS	
Side A - Connector 1	IEC-320-C20
Side B - Connector 1	IEC-320-C13
FEATURES & SPECIFICATIONS	
High Voltage	Yes
Locking Plug	No
Angled Plug	No
STANDARDS & COMPLIANCE	
Certifications	UL/Cul
Approvals	UL/CSA
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

<https://www.tripplite.com/products/product-certification-agencies>