

# PDU Power Cord, C13 to P-Lock Lite C20 - 15A, 100-250V, 14 AWG, 6 ft. (1.8 m), Black

MODEL NUMBER: P032-E06



Connects a computer, server or switch to a PDU with a P-Lock C19 or C39 power connector and extends your existing power connection by 6 ft.

## Features

### Locking C13-to-C20 Power Cable Connects Computers and Servers to a PDU

The P032-E06 power extension cord can be used to power a computer, server, monitor or drive to a UPS system or PDU commonly found in a small data center, office workstation or other lower-amp application. The six-foot (1.8-meter) length helps reduce cable clutter by providing a tailor-made fit between the device and the PDU in a crowded rack enclosure.

### Forms a Special Locking Connection with a P-Lock Outlet

The P-Lock Lite C20 connector forms a secure connection with a PDU with a P-Lock outlet, including Eaton G4 and newer PDUs with C19 and C39 outlets. The P-Lock connection provides a secure connection between equipment and power, reducing the risk of accidental disconnects that cause costly equipment downtime. The P032-E06 lets you replace a non-locking C20/C13 cable or upgrade an entire PDU application by pairing with an Eaton PDU or other PDU with P-Lock outlets.

## Highlights

- Recommended for powering computers, servers and other network devices
- P-Lock Lite C20 connector eliminates accidental cable disconnections in a crowded PDU
- 6 ft. length allows flexibility in mounting devices within a rack while avoiding cable clutter
- PDU-style cord replaces or upgrades non-locking power cable provided by manufacturer

## Package Includes

P032-E06 PDU Power Cord, C13 to P-Lock Lite C20, 6 ft. (1.8 m), Black

## Specifications

OVERVIEW	
UPC Code	037332295330
Device Compatibility	Computer; Monitor/HDTV; PDU; Printer; Server; Tablet; UPS
Country/Region	Global
INPUT	
Maximum Input Amps	15
Voltage Compatibility (VAC)	250
CONNECTIONS	



Powering Business Worldwide

TRIPP LITE  
SERIES

Side A - Connector 1	IEC-320-C13
Side B - Connector 1	IEC-320-C20
<b>PHYSICAL</b>	
Plug Color	Black
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	9.3mm
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm <sup>2</sup> )	2.08
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	13.86 x 8.98 x 0.50
Shipping Weight (lbs.)	0.70
Shipping Weight (kg)	0.32
Unit Dimensions (hwd / in.)	12.800 x 8.900 x 0.500
Unit Weight (lbs.)	1.15
Unit Weight (kg)	0.52
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	23 to 158 F (-5 to 70 C)
Relative Humidity	35 TO 85% RH, Non-Condensing
Operating Humidity Range	10% to 65% RH
Storage Humidity Range	10% to 65% RH
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	Yes
Coiled Power Cord	No



Powering Business Worldwide

TRIPP LITE  
SERIES

P-Lock Power Cord	Yes
Locking Power Cord	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	CAN/CSA C22.2; UL Listed; cUL Listed
Product Compliance	REACH; RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.