

Hospital-Grade Power Cord, NEMA 6-15P to C19 - Heavy-Duty, Green Dot, 15A, 250V, 14 AWG, 6 ft. (1.83 m), Gray

MODEL NUMBER: P033-006-GY-HG



Connects a server, transformer, or other high-current medical device with a C20 power inlet to a grounded 6-15R hospital-grade outlet.

Features

Hospital-Grade Power Cord is a Safe Solution for Medical Facilities This hospital-grade cord features 14 AWG wire suitable for high power connections, making it a reliable solution for devices that require a higher-rated, heavier-gauge cable. The C19 end connects to a server, isolation transformer, power strip or other compatible hospital component. The NEMA 6-15P-HG green-dot plug connects to a hospital-grade AC power source located outside patient-care vicinities. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

Designed and Tested to Strict Hospital-Grade Standards This hospital power cord is tested to ANSI/UL 62 and 817 standards, as well as CAN/CSA C22.2 no. 21 and 49 standards, ensuring it's a dependable power solution for hospital environments.

Color-Coded to Avoid Misidentification That Can Cause Costly Downtime This hospital-grade power cord features a gray SJT jacket and fully molded gray ends. The color-coding allows easy, fast identification in a crowded surge protector and helps prevent the cable from becoming inadvertently disconnected.

Specifications

OVERVIEW	
UPC Code	037332224927
Device Compatibility	Mobile Cart; Computer; Printer; Monitor/HDTV; Server; UPS; PDU
Country/Region	Global
INPUT	

Highlights

- Recommended for connecting devices to power outlets outside patient-care vicinities
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- Hospital-grade power cord replaces or upgrades power cord provided by manufacturer
- Thick 14 AWG wire gauge manages high power levels required for larger equipment
- Color-coded gray for fast, easy identification in a crowded PDU, UPS or surge protector

Applications

- Connect devices like servers, transformers and power strips to an AC outlet up to 6-ft. (1.83 m) away in a hospital environment outside patient-care vicinities
- Extend an existing power connection up to 6-ft. (1.83 m) to more easily place a device or reach a power source
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P033-006-GY-HG Hospital-Grade Power Cord, NEMA 6-15P to C19, 6-ft. (1.83 m), Gray

Maximum Input Amps	15
Voltage Compatibility (VAC)	100-250
PHYSICAL	
Plug Color	Gray
Cable Jacket Color	Gray
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	9.2mm
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm ²)	2.08
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	1.00 x 9.00 x 13.00
Shipping Dimensions (hwd / cm)	2.54 x 22.86 x 33.02
Shipping Weight (lbs.)	0.80
Shipping Weight (kg)	0.36
ENVIRONMENTAL	
Operating Temperature Range	-4° to 221°F (-20° to 105°C)
Storage Temperature Range	-4° to 221°F (-20° to 105°C)
Operating Humidity Range	0% to 65% RH
Storage Humidity Range	0% to 65% RH
CONNECTIONS	
Side A - Connector 1	NEMA 6-15P-HG
Side B - Connector 1	IEC-320-C19
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No

TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard
Cleveland, OH 44122
United States

STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); cUL Listed; UL Listed
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

TRIPP-LITE

by **EAT•N**

© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.