

Power Extension Cord, C19 to C20 - Heavy-Duty, 20A, 250V, 12 AWG, 2 ft. (0.61 m), Black

MODEL NUMBER: P036-002



C19 to C20 20A heavy-duty extension cable connects high-output devices with C19/C20 power connectors, including blade server chassis.

Features

20A C20-to-C19 Power Cable for Network Devices That Require a Heavy-Gauge Connection This heavy-duty extension cord features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This cord can be used to connect a server, router, network switch or blade server enclosure to a UPS system or PDU or replace or upgrade the standard power cord provided by the device's manufacturer. The 2-ft. (0.61 m) length helps reduce cable clutter and minimize the risk of tripping.

Highlights

- Recommended for powering servers, routers and other high-output network devices
- 2-ft. (0.61 m) length allows flexibility in placing devices, while avoiding cable clutter
- C20 to C19 cord replaces or upgrades standard power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment

Applications

- Connect devices like computers, servers and monitors to a PDU up to 2-ft. (0.61 m) away in your data center
- Extend an existing power connection up to 2-ft. (0.61 m) to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P036-002 C19 to C20 Heavy-Duty Extension Cord, 2-ft. (0.61 m), Black

Specifications

| OVERVIEW | |
|----------------------|--|
| UPC Code | 037332141613 |
| Device Compatibility | Server; Router; Network Switch; UPS; PDU |
| Country/Region | North America |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| INPUT | |
|-------------------------------------|---------------------------|
| Maximum Input Amps | 20 |
| Voltage Compatibility (VAC) | 250 |
| PHYSICAL | |
| Color | Black |
| Number of Conductors | 3 |
| Wire Gauge (AWG) | 12 |
| Wire Gauge (OD - mm ²) | 3.31 |
| Cable Length (ft.) | 2 |
| Cable Length (m) | 0.6 |
| Power Cord Jacket Type | SJT |
| Shipping Dimensions (hwd / cm) | 32.51 x 22.61 x 1.27 |
| Shipping Dimensions (hwd / in.) | 12.80 x 8.90 x 0.50 |
| Shipping Weight (kg) | 0.25 |
| Shipping Weight (lbs.) | 0.55 |
| CONNECTIONS | |
| Side A - Connector 1 | IEC-320-C20 |
| Side B - Connector 1 | IEC-320-C19 |
| SPECIAL FEATURES | |
| High Voltage | Yes |
| Locking Plug | No |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>