



Power Extension Cord, C19 to C20 - Heavy-Duty, 20A, 250V, 12 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: P036-006









C19 to C20 20A heavy-duty extension cable connects high-output devices with C19/C20 power connectors, including blade server chassis.

Features

20A C20-to-C19 Power Cable for Network Devices That Require a Heavy-Gauge ConnectionThis heavy-duty extension cord features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This cord can be used to connect a server, router, network switch or blade server enclosure to a UPS system or PDU or replace or upgrade the standard power cord provided by the device's manufacturer. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

Highlights

- Recommended for powering servers, routers and other highoutput network devices
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- C20 to C19 cord replaces or upgrades standard power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment

Applications

- Connect devices like computers, servers and monitors to a PDU up to 6-ft. (1.83 m) away in your data center
- Extend an existing power connection up to 6-ft. (1.83 m) to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

 P036-006 C19 to C20 Heavy-Duty Extension Cord, 6-ft. (1.83 m), Black

Specifications

•		
OVERVIEW		
OVERVIEW		
UPC Code	037332141620	
Device Compatibility	Server; Router; Network Switch; UPS; PDU	
Country/Region	North America	
INPUT		
Maximum Input Amps	20	
Voltage Compatibility (VAC)	100-250	
CONNECTIONS		
Side A - Connector 1	IEC-320-C20	
Side B - Connector 1	IEC-320-C19	
PHYSICAL		





Plug Color	Black	
Cable Jacket Color	Black	
Cable Jacket Material	PVC	
Cable Jacket Rating	VW-1	
Power Cord Jacket Type	SJT	
Cable Outer Diameter (OD)	11mm	
Number of Conductors	3	
Wire Gauge (AWG)	12	
Wire Gauge (OD - mm²)	3.31	
Cable Length (ft.)	6	
Cable Length (m)	1.83	
Shipping Dimensions (hwd / in.)	1.00 x 7.00 x 11.00	
Shipping Dimensions (hwd / cm)	2.54 x 17.78 x 27.94	
Shipping Weight (lbs.)	1.02	
Shipping Weight (kg)	0.46	
ENVIRONMENTAL		
Operating Temperature Range	-4° to 140°F (-20° to 60°C)	
Storage Temperature Range	-4° to 140°F (-20° to 60°C)	
Operating Humidity Range	10% to 65% RH	
Storage Humidity Range	10% to 65% RH	
FEATURES & SPECIFICATIONS		
Antibacterial	No	
Angled Plug	No	
High Voltage	Yes	
Locking Plug	No	
Coiled Power Cord	No	
STANDARDS & COMPLIANCE		
Product Certifications	cUL Listed; UL Listed	
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	





1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.