

# Power Extension Cord/Splitter, 2 x C19 to C20 Y Splitter - Heavy-Duty, 20A, 250V, 12 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: P036-006-2C19



C19-to-C20 splitter allows 2 devices with C20 inlets to share one AC power input cord and one C19 outlet on a PDU or UPS system.

## Features

**Heavy-Duty Y-Style Splitter Cable Connects 2 Devices with C20 Inlets to One C19 Outlet** This heavy-duty splitter extension cord features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This cord features a C20 plug for connecting to an AC power source and two C19 pigtails for connecting to devices. By connecting two devices to one outlet, the power cord splitter frees up space in a PDU, UPS system or surge protector and helps reduce cable clutter. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

**Dual IEC Cable Powers a Wide Variety of Essential Electronics** With this 20A power splitter, a single C19 outlet can power two high-output devices, such as servers, routers, blade server chassis and other equipment compatible with a C19 connector. Ideal for areas where AC outlets are limited, such as rack cabinets, this cable is compatible with most power and extension cords.

## Specifications

OVERVIEW	
UPC Code	037332156549
Device Compatibility	Server; Router; Network Switch; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	20
Voltage Compatibility (VAC)	100-250

## Highlights

- Connects 2 devices to one AC outlet to save space and reduce cable clutter
- Recommended for powering servers, routers and other high-output network devices
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- C20 to C19 cord replaces or upgrades standard power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment

## Applications

- Connect 2 devices like high-power servers, routers and blade server chassis to one power outlet up to 6-ft. (1.83 m) away in your network setup
- Save space in a 0U vertical rack-mount PDU by plugging two rack devices into one outlet
- Update or replace the standard power cords provided by your devices' original manufacturer

## Package Includes

- P036-006-2C19 2x C19 to C20 Y Splitter Heavy-Duty Power Extension Cord, 6-ft. (1.83 m), Black



Powering Business Worldwide

TRIPP LITE  
SERIES

CONNECTIONS	
Side A - Connector 1	IEC-320-C20
Side B - Connector 1	(2) IEC-320-C19
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	11.2mm
Number of Conductors	3
Wire Gauge (AWG)	12
Wire Gauge (OD - mm <sup>2</sup> )	3.31
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	1.00 x 5.60 x 8.50
Shipping Dimensions (hwd / cm)	2.54 x 14.22 x 21.59
Shipping Weight (lbs.)	0.90
Shipping Weight (kg)	0.41
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	14° to 140°F (-10° to 60°C)
Operating Humidity Range	35% to 85% RH, Non-Condensing
Storage Humidity Range	35% to 85% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS



Powering Business Worldwide

TRIPP LITE  
SERIES

**WARRANTY & SUPPORT**

Product Warranty Period  
(Worldwide)

Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.