

## Power Cord Adapter, NEMA L5-20R to NEMA 5-20P - Heavy-Duty, 20A, 120V, 12 AWG, 6-in. (15.24 cm), Black

MODEL NUMBER: P044-06I



L5-20R to 5-20P heavy-duty power adapter transforms a NEMA 5-15/20R straight-blade outlet to a locking L5-20R outlet.

### Features

**Heavy-Duty Power Adapter Connects Devices That Require a Heavy-Gauge Connection** This heavy-duty adapter features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. The six-inch power adapter transforms a NEMA 5-15/20R straight-blade outlet into a locking L5-20R outlet. It is also a recommended replacement or upgrade of a standard power cord provided by the device's manufacturer.

**Locking L5-20R Connector Helps Prevent Accidental Disconnection and Expensive Downtime** Having a cable come loose accidentally can mean the loss of power and costly downtime. The locking NEMA L5-20R connector helps you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking adapter is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

## Specifications

OVERVIEW	
UPC Code	037332139115
Device Compatibility	Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	20
Voltage Compatibility (VAC)	125

### Highlights

- 6 in. adapter allows easy transition to L5-20R outlet with no electrician needed
- Heavy-duty cable replaces or upgrades standard power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment
- Locking connector maintains secure link to avoid loss of power and costly downtime

### Applications

- Transform a non-locking outlet into a locking outlet to prevent a power loss due to accidental disconnection
- Update or replace the standard power cord provided by a device's original manufacturer

### Package Includes

- P044-06I L5-20R to 5-20P Heavy-Duty Power Adapter, 6 in., Black



<b>PHYSICAL</b>	
Cable Jacket Color	Black
Cable Jacket Material	PVC
Plug Color	Black
Power Cord Jacket Type	SJT
Cable Jacket Rating	VW-1
Number of Conductors	3
Wire Gauge (AWG)	12
Wire Gauge (OD - mm <sup>2</sup> )	3.31
Cable Length (ft.)	0.5
Cable Length (m)	0.1524
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / cm)	25.40 x 17.78 x 0.25
Shipping Dimensions (hwd / in.)	10.00 x 7.00 x 0.10
Shipping Weight (kg)	0.18
Shipping Weight (lbs.)	0.40
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Storage Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Operating Humidity Range	10 TO 65% RH
Storage Humidity Range	10 TO 65% RH
<b>CONNECTIONS</b>	
Side A - Connector 1	NEMA 5-20P
Side B - Connector 1	NEMA L5-20R
<b>FEATURES &amp; SPECIFICATIONS</b>	
High Voltage	No
Locking Plug	No
Angled Plug	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	UL/Cul
Approvals	UL/CSA



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>