

## Power Cord, C19 to NEMA L5-20P - Heavy-Duty, 20A, 125V, 12 AWG, 10 ft. (3.05 m), Black

MODEL NUMBER: P045-010



Heavy-duty extension cord transforms a C20 plug into a locking NEMA L5-20P plug and extends an existing connection up to 10 ft.

### Features

**Heavy-Duty Extension Cable Connects Devices That Require a Heavy-Gauge Connection** This heavy-duty extension cord features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This C19 to L5-20P cord transforms a non-locking plug into a locking plug and can be used to connect a high-output device to a wall outlet or a PDU or UPS with L5-20R outlets. It is also a recommended replacement or upgrade of a standard power cord provided by the device's manufacturer. The 10-ft. (3.05 m) length allows you great flexibility in placing equipment with respect to the power outlet.

**Locking L5-20P Connector Helps Prevent Accidental Disconnection and Expensive Downtime** Having a cable come loose accidentally can mean the loss of power and costly downtime. The locking connector helps you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

## Specifications

OVERVIEW	
UPC Code	037332140937
Device Compatibility	Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	20
Voltage Compatibility (VAC)	125

### Highlights

- 10-ft. (3.05 m) length allows great flexibility in placing devices in relationship to AC outlet
- Heavy-duty cable replaces or upgrades standard power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment
- Locking connector maintains secure link to avoid loss of power and costly downtime

### Applications

- Connect devices to a power outlet up to 10-ft. (3.05 m) away in your office or workspace
- Transform a non-locking C20P plug into a locking L5-20P plug to prevent a power loss due to accidental disconnection
- Extend an existing power connection up to 10-ft. (3.05 m) to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

### Package Includes

- P045-010 C19 to L5-20P Heavy-Duty Extension Cord, 10-ft. (3.05 m), Black



Powering Business Worldwide

TRIPP LITE  
SERIES

CONNECTIONS	
Side A - Connector 1	NEMA L5-20P
Side B - Connector 1	IEC-320-C19
PHYSICAL	
Color	Black
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	11mm
Number of Conductors	3
Wire Gauge (AWG)	12
Wire Gauge (OD - mm <sup>2</sup> )	3.31
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	10.98 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	27.89 x 17.78 x 1.27
Shipping Weight (lbs.)	1.72
Shipping Weight (kg)	0.78
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Relative Humidity	10% to 65% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS



Powering Business Worldwide

TRIPP LITE  
SERIES

**WARRANTY & SUPPORT**

Product Warranty Period  
(Worldwide)

Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.