

## Power Extension Cord, NEMA L5-30P to NEMA L5-30R- Heavy-Duty, 30A, 125V, 10 AWG, 6 ft. (1.83 m), Black, Locking Connectors

MODEL NUMBER: P046-006-LL-30A



### Highlights

- Locking connectors prevent accidental disconnection
- Durable PVC jacket
- 6-ft. (1.83 m) long
- 125V/30A rating

### Package Includes

- P046-006-LL-30A Heavy-Duty Power Extension Cord, 6-ft. (1.83 m)

Extends the length of your existing power cord with NEMA L5-30P plug by 6 ft.

### Description

The P046-006-LL-30A Heavy-Duty Power Extension Cord features a NEMA L5-30P plug on one end and a NEMA L5-30R receptacle on the other, allowing you to extend the length of your existing power cord. Both molded connectors twist and lock into place, which prevents disconnection via jostling or other accidental impact. The 6-ft. (1.83 m) 10 AWG cord is rated for 125V and 30A. Its durable PVC jacket is designed to last a long time.

### Features

#### Extends Existing Power Cord with NEMA L5-30P Plug

- NEMA L5-30R receptacle at opposite end
- Molded locking connectors prevent accidental disconnection
- Integral strain relief
- 125V/30A rating
- Durable PVC jacket
- 6-ft. (1.83 m) long

## Specifications

OVERVIEW	
UPC Code	037332200938
Device Compatibility	UPS; PDU



Country/Region	North America
<b>INPUT</b>	
Maximum Input Amps	30
Voltage Compatibility (VAC)	125
<b>PHYSICAL</b>	
Color	Black
Number of Conductors	3
Wire Gauge (AWG)	10
Wire Gauge (OD - mm <sup>2</sup> )	5.26
Cable Length (ft.)	6
Cable Length (m)	1.8
Cable Length (in.)	72
Cable Length (cm)	182.88
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	29.21 x 22.86 x 1.27
Shipping Dimensions (hwd / in.)	11.50 x 9.00 x 0.50
Shipping Weight (kg)	0.86
Shipping Weight (lbs.)	1.90
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	41 F TO 95 F (5 C TO 35 C)
Storage Temperature Range	41 F TO 95 F (5 C TO 35 C)
Operating Humidity Range	0-65% RH
Storage Humidity Range	0-65% RH
<b>CONNECTIONS</b>	
Side A - Connector 1	NEMA L5-30P
Side B - Connector 1	NEMA L5-30R
<b>SPECIAL FEATURES</b>	
High Voltage	No
Locking Plug	Yes
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>