

# Power Cord Adapter, NEMA L5-20P to NEMA 5-20R - Heavy-Duty, 20A, 125V, 12 AWG, 6-in. (15.24 cm), Black

MODEL NUMBER: P046-06N



Heavy-duty extension cord connects your computer or other device with a NEMA 5-20P plug to a NEMA L5-20R outlet.

## Features

**Heavy-Duty Extension Cable for Network Devices That Require a Heavy-Gauge Connection** This six-inch cord features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. It can be used to connect a computer, server or other device with a NEMA 5-20P plug to a wall outlet, PDU or UPS system with a NEMA L5-20R outlet. The short length helps reduce cable clutter.

**Locking Connector Helps Prevent Accidental Disconnection and Expensive Downtime** Having a cable come loose accidentally can mean the loss of power and costly downtime. The locking connector helps you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

## Specifications

OVERVIEW	
UPC Code	037332158321
Device Compatibility	Computer; Monitor/HDTV; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	20
Voltage Compatibility (VAC)	125
CONNECTIONS	

## Highlights

- Recommended for powering computers, servers and other network devices
- Heavy-duty cord replaces or upgrades standard power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment
- Locking connector maintains secure link to avoid loss of power and costly downtime

## Applications

- Connect devices like computers, servers and monitors to a PDU in your data center
- Update or replace the standard power cord provided by a device's original manufacturer

## Package Includes

- P046-06N L5-20P to 5-20R Heavy-Duty Extension Cord, 6 in., Black



Powering Business Worldwide

TRIPP LITE  
SERIES

Side A - Connector 1	NEMA L5-20P
Side B - Connector 1	NEMA 5-20R
<b>PHYSICAL</b>	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	11mm
Number of Conductors	3
Wire Gauge (AWG)	12
Wire Gauge (OD - mm <sup>2</sup> )	3.31
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	10.00 x 7.10 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 18.03 x 1.27
Shipping Weight (lbs.)	0.40
Shipping Weight (kg)	0.18
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 80% RH
Storage Humidity Range	20% to 80% RH
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS



Powering Business Worldwide

TRIPP LITE  
SERIES

**WARRANTY & SUPPORT**

Product Warranty Period  
(Worldwide)

Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.