

Power Cord, C19 to C14 - Heavy Duty, 15A, 250V, 14 AWG, 4 ft., Black

MODEL NUMBER: P047-004



C14 to C19 power cord transforms a C20 plug into a C14 plug for connecting to a C13 outlet on a PDU or UPS system.

Features

C19 to C14 Power Cord for Network Devices That Require a Heavy-Gauge Connection This C14 to C19 cable features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. The C14 to C19 power cable can be used to connect a computer, server or drive to a UPS system or PDU or replace or upgrade the standard power cord provided by the device's manufacturer. The four-foot length helps reduce cable clutter and minimize the risk of tripping.

Highlights

- C19 to C14 cable for powering computers, servers and other network devices
- 4 ft. length allows flexibility in placing devices, while avoiding cable clutter
- Heavy-duty cable replaces or upgrades standard power cord provided by manufacturer
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

Applications

- Connect devices like computers, servers and drives to a PDU up to 4 ft. away in your data center
- Extend an existing power connection up to 4 ft. to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P047-004 C19 to C14 Power Cord, 4 ft., Black

Specifications

OVERVIEW	
UPC Code	037332150042
Country/Region	North America
INPUT	
Maximum Input Amps	15



Cable Length (ft.)	4
Cable Length (m)	1.2
Voltage Compatibility (VAC)	100-250
PHYSICAL	
Color	Black
Number of Conductors	3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	32.51 x 22.61 x 1.27
Shipping Dimensions (hwd / in.)	12.80 x 8.90 x 0.50
Shipping Weight (kg)	0.27
Shipping Weight (lbs.)	0.60
Wire Gauge (AWG)	14
Wire Gauge (OD - mm ²)	2.08
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C19
SPECIAL FEATURES	
High Voltage	Yes
Locking Plug	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>