

## C19 to 5-20P Heavy-Duty Extension Cord - 20A, 125V, 12 AWG, 10 ft., Black

MODEL NUMBER: P049-010



Heavy-duty extension cord transforms a C20 plug into a NEMA 5-20P plug and extends an existing connection up to 10 ft.

### Features

**Heavy-Duty Extension Cable Connects Devices That Require a Heavy-Gauge Connection** This heavy-duty extension cord features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This C19 to 5-20P cord can be used to connect a high-output device to a wall outlet or a PDU or UPS with 5-20R outlets. It is also a recommended replacement or upgrade of a standard power cord provided by the device's manufacturer. The 10-foot length allows you great flexibility in placing equipment with respect to the power outlet.

### Highlights

- 10 ft. length allows great flexibility in placing devices in relationship to AC outlet
- Heavy-duty cable replaces or upgrades standard power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment

### Applications

- Connect devices to a power outlet up to 10 ft. away in your office or work space
- Transform a C20 plug into a NEMA 5-20P plug with no electrician needed
- Extend an existing power connection up to 10 ft. to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

### Package Includes

- P049-010 C19 to 5-20P Heavy-Duty Extension Cord, 10 ft., Black

## Specifications

OVERVIEW	
UPC Code	037332140944
Country/Region	North America
INPUT	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Maximum Input Amps	20
Cable Length (ft.)	10
Cable Length (m)	3.1
Voltage Compatibility (VAC)	125
<b>PHYSICAL</b>	
Power Cord Jacket Type	SJT
Wire Gauge (AWG)	12
Wire Gauge (OD - mm <sup>2</sup> )	3.31
Shipping Dimensions (hwd / in.)	12.80 x 8.90 x 0.10
Shipping Dimensions (hwd / cm)	32.51 x 22.61 x 0.25
Shipping Weight (lbs.)	1.70
Shipping Weight (kg)	0.77
Color	Black
Number of Conductors	3
<b>CONNECTIONS</b>	
Side A - Connector 1	NEMA 5-20P
Side B - Connector 1	IEC-320-C19
<b>SPECIAL FEATURES</b>	
High Voltage	No
Heavy-Duty	Yes
Locking Plug	No
<b>CERTIFICATIONS</b>	
Approvals	UL-approved
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>