

EU Computer Power Cord , C19 to Schuko - 16A, 250V, 16 AWG, 8 ft. (2.43 m), Black

MODEL NUMBER: P050-008



IEC 320 C19 to Schuko EU power cord transforms a C20 plug into a Schuko plug for connecting to a wall outlet, PDU or UPS system.

Features

C19 to Schuko EU Power Cord Connects Computers, Servers and Other Network Devices This C19 to Schuko European power cord is designed for small data center or office workstation applications that do not require a heavy-gauge connection. The cable can be used to connect a computer, server or drive to a Schuko wall outlet, UPS system or PDU or replace or upgrade a worn-out or lost power cable. The 8-ft. (2.43 m) length allows you flexibility in placing equipment with respect to the power outlet.

Highlights

- C19 to Schuko cable for powering computers, servers and other network devices
- 8-ft. (2.43 m) length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for worn-out or missing EU power cable

Applications

- Connect devices like computers, servers and drives to a PDU up to 2.4 m away in your data center
- Transform a C20 plug into a Schuko plug with no electrician needed
- Extend an existing power connection up to 2.4 m to more easily place a device or reach a power source in a rack
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P050-008 C19 to Schuko, EU Power Cord, 8-ft. (2.43 m), Black

Specifications

OVERVIEW	
UPC Code	037332141989
Device Compatibility	Computer; Server; UPS; PDU
Country/Region	Europe
INPUT	
Maximum Input Amps	16
Voltage Compatibility (VAC)	250
CONNECTIONS	
Side A - Connector 1	CEE 7/7 SCHUKO PLUG
Side B - Connector 1	IEC-320-C19
PHYSICAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Power Cord Jacket Type	H05VV-F
Cable Outer Diameter (OD)	8.2mm
Number of Conductors	2
Wire Gauge (AWG)	16
Wire Gauge (OD - mm ²)	1.29
Cable Length (ft.)	8
Cable Length (m)	2.44
Shipping Dimensions (hwd / in.)	0.50 x 8.90 x 12.50
Shipping Dimensions (hwd / cm)	1.27 x 22.61 x 31.75
Shipping Weight (lbs.)	0.80
Shipping Weight (kg)	0.36
Unit Dimensions (hwd / in.)	0.500 x 8.900 x 12.500
ENVIRONMENTAL	
Operating Temperature Range	23° to 140°F (-5° to 60°C)
Storage Temperature Range	-4° to 176°F (-20° to 80°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	CE (Europe); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.