

UK Computer Power Cord, BS 1363 to C19 - 13A, 250V, H05VV-F, 2.5 m (8.2 ft.), Black

MODEL NUMBER: P052-2P5M-UK



Connects a switch or blade server with a C20 inlet to a PDU or UPS with BS 1363 outlets.

Features

UK Power Cord Connects Data Center Equipment to Reliable AC Power

This VDE-compliant power cable connects a switch, router, blade server or other device with a C20 inlet to a PDU, UPS system or surge protector with BS 1363 outlets. It can also extend an existing power connection up to 2.5 meters (8.2 feet). The P052-2P5M-UK features a BS 1363 end for connecting to an AC power source and an IEC-320-C19 end for connecting to a network device in a data center or other IT application.

H05VV-F Jacket Is Fully VDE-Compatible for European Applications

The 0.75mm² enhanced PVC jacket complies with VDE, CE and UKCA standards for data centers, racks, workstations and other IT applications in Europe.

Highlights

- Recommended for powering switches, blade servers and other network devices
- 2.5-meter length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for a worn-out or missing power cord
- VDE-compliant H05VV-F jacket allows use in European IT applications

Package Includes

P052-2P5M-UK C19 to BS 1363 UK Power Cable with BS 1363 Plug, 2.5 m (8.2 ft.), Black

Specifications

OVERVIEW	
UPC Code	037332281067
Product Type	Power Cord
Device Compatibility	PDU; Server; UPS
Country/Region	UK
INPUT	
Maximum Input Amps	13.0
Voltage Compatibility (VAC)	250
CONNECTIONS	
Side A - Connector 1	BS1363 UK PLUG



Powering Business Worldwide

TRIPP LITE
SERIES

Side B - Connector 1	IEC-320-C19
PHYSICAL	
Plug Color	Black
Cable Jacket Material	PVC
Power Cord Jacket Type	H05VV-F
Cable Outer Diameter (OD)	8.2 mm
Number of Conductors	3
Conductor Gauge	48/0.2AS
Wire Gauge (AWG)	16
Wire Gauge (OD - mm ²)	1.5
Power Cord Color	Black
Cable Length (ft.)	8.20
Cable Length (m)	2.50
Cable Length (cm)	250
Shipping Dimensions (hwd / in.)	10.00 x 7.99 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 20.29 x 1.27
Shipping Weight (lbs.)	0.82
Shipping Weight (kg)	0.37
Unit Dimensions (hwd / in.)	10.000 x 7.990 x 0.500
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.441
Unit Weight (kg)	0.20
ENVIRONMENTAL	
Operating Temperature Range	5° to 158° F (-15° to 70° C)
Storage Temperature Range	5° to 140° F (-15° to 60° C)
Operating Humidity Range	20% TO 80% RH, NON-CONDENSING
Storage Humidity Range	20% TO 80% RH, NON-CONDENSING
FEATURES & SPECIFICATIONS	
Antibacterial	No
Armored Cable	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No



Powering Business Worldwide

TRIPP LITE
SERIES

Locking	No
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.