

## UK Computer Power Cord, BS 1363 to C19 - 13A, 250V, H05VV-F, 2.5 m (8.2 ft.), Black

MODEL NUMBER: P052-2P5M-UK



Connects a switch or blade server with a C20 inlet to a PDU or UPS with BS 1363 outlets.

### Features

#### UK Power Cord Connects Data Center Equipment to Reliable AC Power

This VDE-compliant power cable connects a switch, router, blade server or other device with a C20 inlet to a PDU, UPS system or surge protector with BS 1363 outlets. It can also extend an existing power connection up to 2.5 meters (8.2 feet). The P052-2P5M-UK features a BS 1363 end for connecting to an AC power source and an IEC-320-C19 end for connecting to a network device in a data center or other IT application.

#### H05VV-F Jacket Is Fully VDE-Compatible for European Applications

The 0.75mm<sup>2</sup> enhanced PVC jacket complies with VDE, CE and UKCA standards for data centers, racks, workstations and other IT applications in Europe.

## Specifications

OVERVIEW	
UPC Code	037332281067
Product Type	Power Cord
Device Compatibility	PDU; Server; UPS
Country/Region	UK
INPUT	
Maximum Input Amps	13.0
Voltage Compatibility (VAC)	250
PHYSICAL	

### Highlights

- Recommended for powering switches, blade servers and other network devices
- 2.5-meter length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for a worn-out or missing power cord
- VDE-compliant H05VV-F jacket allows use in European IT applications

### Package Includes

P052-2P5M-UK C19 to BS 1363  
UK Power Cable with BS 1363  
Plug, 2.5 m (8.2 ft.), Black

Plug Color	Black
Cable Jacket Material	PVC
Power Cord Jacket Type	H05VV-F
Cable Outer Diameter (OD)	8.2 mm
Number of Conductors	3
Conductor Gauge	48/0.2AS
Wire Gauge (AWG)	16
Wire Gauge (OD - mm <sup>2</sup> )	1.5
Power Cord Color	Black
Cable Length (ft.)	8.20
Cable Length (m)	2.50
Cable Length (cm)	250
Shipping Dimensions (hwd / in.)	10.00 x 7.99 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 20.29 x 1.27
Shipping Weight (lbs.)	0.82
Shipping Weight (kg)	0.37
Unit Dimensions (hwd / in.)	10.000 x 7.990 x 0.500
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.441
Unit Weight (kg)	0.20
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	5° to 158° F (-15° to 70° C)
Storage Temperature Range	5° to 140° F (-15° to 60° C)
Operating Humidity Range	20% TO 80% RH, NON-CONDENSING
Storage Humidity Range	20% TO 80% RH, NON-CONDENSING
<b>CONNECTIONS</b>	
Side A - Connector 1	BS1363 UK PLUG
Side B - Connector 1	IEC-320-C19
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Armored Cable	No
Angled Plug	No
High Voltage	Yes

Locking Plug	No
Coiled Power Cord	No
Locking	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	CE (Europe); REACH; RoHS; UKCA
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty