

China Computer Power Cord, GB 15934-2008 to C13 - 10A, 250V, 17 AWG, 10 ft. (3.05 m), Black

MODEL NUMBER: P055-010-CHN1



C13 to GB 15934-2008 power cord transforms a C14 plug into a GB 15934-2008 plug for connecting to a grounded AC power outlet in China.

Features

C13 to GB 15934-2008 Power Cord Connects Servers and Other Network Devices This GB 15934-2008 to C13 Chinese computer power cord with molded ends is designed for small data center or office workstation applications that do not require a heavy-gauge connection. The cable can be used to connect a computer, server or drive to a GB 15934-2008 grounded wall outlet or replace or upgrade a worn-out or lost Chinese power cable. The 10-ft. (3.05 m) (3-meter) length allows you great flexibility in placing equipment with respect to the power outlet.

Specifications

OVERVIEW	
UPC Code	037332232656
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	China
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	250
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC

Highlights

- C13 to GB 15934-2008 cable for powering computers, servers and other network devices
- 10-ft. (3.05 m) length allows great flexibility in placing devices in relationship to AC outlet
- Ideal replacement for worn-out or missing Chinese power cable

Applications

- Connect devices like computers, servers and printers to an outlet up to 3 m away in a hotel room or conference room in China
- Transform a C14 plug into a GB 15934-2008 plug with no electrician needed
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P055-010-CHN1 C13 to GB 15934-2008, China Computer Power Cord, 10-ft. (3.05 m), Black

Power Cord Jacket Type	PVC
Cable Outer Diameter (OD)	7.0mm
Number of Conductors	3
Wire Gauge (AWG)	17
Wire Gauge (OD - mm ²)	1.15
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	12.80 x 8.86 x 0.50
Shipping Dimensions (hwd / cm)	32.51 x 22.50 x 1.27
Shipping Weight (lbs.)	0.65
Shipping Weight (kg)	0.29
ENVIRONMENTAL	
Operating Temperature Range	23 F TO 140 F (-5 C TO 60 C)
Storage Temperature Range	-4 F TO 176 F (-20 C TO 80C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	GB 15934-2008
Side B - Connector 1	IEC-320-C13
FEATURES & SPECIFICATIONS	
High Voltage	Yes
Locking Plug	No
Antibacterial	No
Angled Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2022 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.