

UK Computer Power Cord, BS1363 to C13 - 10A, 250V, 18 AWG, 6 ft. (1.8 m), Black

MODEL NUMBER: P056-006-10A



UK computer power cord connects your computer or peripheral with a C14 inlet to any grounded AC power outlet that accepts BS1363 plugs.

Features

UK IEC Power Cord Connects Computers, Servers and Other Network Devices

This BS1363 to C13 UK computer power cord is designed for small data center or office workstation applications that do not require a heavy-gauge connection. The cable can be used to connect a computer, server or drive to a BS1363 wall outlet, UPS system or PDU or replace or upgrade a worn-out or lost power cable. The six-foot (1.8-meter) length allows you flexibility in placing equipment with respect to the power outlet.

Highlights

- BS1363 to C13 cable for powering computers, servers and other network devices
- 6 ft. (1.8 m) length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for worn-out or missing UK computer power cable

Applications

- Connect devices like computers, monitors and printers to a PDU up to 6 ft. (1.8 m) away in your home or office workstation
- Extend an existing power connection up to 6 ft. (1.8 m) to more easily place a device or reach a power source in a rack
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P056-006-10A BS1363 to C13, UK IEC Power Cable, 6 ft. (1.8 m), Black

Specifications

OVERVIEW	
UPC Code	037332190796
Country/Region	UK
INPUT	
Maximum Input Amps	10
Cable Length (ft.)	6



Cable Length (m)	1.8
Voltage Compatibility (VAC)	250
PHYSICAL	
Color	Black
Number of Conductors	3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	18.01 x 19.99 x 1.27
Shipping Dimensions (hwd / in.)	7.09 x 7.87 x 0.50
Shipping Weight (kg)	0.27
Shipping Weight (lbs.)	0.60
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	1.15
CONNECTIONS	
Side A - Connector 1	BS1363 UK PLUG
Side B - Connector 1	IEC-320-C13
SPECIAL FEATURES	
High Voltage	Yes
Locking Plug	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>