

PDU Power Cord, BS 1363 to C13 - 10A, 250V, H05VV-F, 2 m (6.6 ft.), Black

MODEL NUMBER: P056-02M-UK



Connects a PDU or UPS system with a C14 inlet to a BS 1363 wall outlet.

Features

Power Cord Connects Data Center Equipment to Reliable AC Power

This VDE-compliant power cable connects a PDU or UPS system with a C14 inlet to a BS 1363 wall outlet. It can also connect a computer, server, monitor or other device to a PDU, UPS or surge protector with BS 1363 outlets. Or you can extend an existing power connection up to two meters (6.6 feet). The P056-02M-UK features a BS 1363 end for connecting to an AC power source and an IEC-320-C13 end for connecting to a network device in a data center or other IT application.

H05VV-F Jacket Is Fully VDE-Compatible for European Applications

The 0.75mm² enhanced PVC jacket complies with VDE, CE and UKCA standards for data centers, racks, workstations and other IT applications in Europe.

Specifications

OVERVIEW	
UPC Code	037332280947
Product Type	Power Extension Cord
Device Compatibility	Computer; PDU; Server
Country/Region	UK
INPUT	
Maximum Input Amps	10.0
Voltage Compatibility (VAC)	250
PHYSICAL	

Highlights

Also recommended for connecting PCs, monitors and servers to AC power. Ideal replacement for a worn-out or missing power cord. VDE-compliant H05VV-F jacket allows use in European IT applications.

Package Includes

P056-02M-UK C13 to BS 1363 PDU Power Cable, 2 m (6.6 ft.), Black

Plug Color	Black
Cable Jacket Material	PVC
Power Cord Jacket Type	H05VV-F
Cable Outer Diameter (OD)	6.7 mm
Number of Conductors	3
Conductor Gauge	24/0.20AS
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.75
Power Cord Color	Black
Cable Length (ft.)	6.56
Cable Length (m)	2.00
Cable Length (cm)	100
Shipping Dimensions (hwd / in.)	9.02 x 7.01 x 0.50
Shipping Dimensions (hwd / cm)	22.91 x 17.81 x 1.27
Shipping Weight (lbs.)	0.49
Shipping Weight (kg)	0.22
Unit Dimensions (hwd / in.)	9.020 x 7.010 x 0.500
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.48
Unit Weight (kg)	0.22
ENVIRONMENTAL	
Operating Temperature Range	5° to 158° F (-15° to 70° C)
Storage Temperature Range	5° to 140° F (-15° to 60° C)
Operating Humidity Range	20% TO 80% RH, NON-CONDENSING
Storage Humidity Range	20% TO 80% RH, NON-CONDENSING
CONNECTIONS	
Side A - Connector 1	BS1363 UK PLUG
Side B - Connector 1	IEC-320-C13
FEATURES & SPECIFICATIONS	
Antibacterial	No
Armored Cable	No
Angled Plug	No
High Voltage	Yes

Locking Plug	No
Coiled Power Cord	No
Locking	No
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty