

PDU Power Cord, BS 1363 to C13 - 10A, 250V, H05VV-F, 2 m (6.6 ft.), Black

MODEL NUMBER: P056-02M-UK



Connects a PDU or UPS system with a C14 inlet to a BS 1363 wall outlet.

Features

Power Cord Connects Data Center Equipment to Reliable AC Power

This VDE-compliant power cable connects a PDU or UPS system with a C14 inlet to a BS 1363 wall outlet. It can also connect a computer, server, monitor or other device to a PDU, UPS or surge protector with BS 1363 outlets. Or you can extend an existing power connection up to two meters (6.6 feet). The P056-02M-UK features a BS 1363 end for connecting to an AC power source and an IEC-320-C13 end for connecting to a network device in a data center or other IT application.

H05VV-F Jacket Is Fully VDE-Compatible for European Applications

The 0.75mm² enhanced PVC jacket complies with VDE, CE and UKCA standards for data centers, racks, workstations and other IT applications in Europe.

Highlights

Also recommended for connecting PCs, monitors and servers to AC power. Ideal replacement for a worn-out or missing power cord. VDE-compliant H05VV-F jacket allows use in European IT applications.

Package Includes

P056-02M-UK C13 to BS 1363 PDU Power Cable, 2 m (6.6 ft.), Black

Specifications

| OVERVIEW | |
|-----------------------------|-----------------------|
| UPC Code | 037332280947 |
| Product Type | Power Extension Cord |
| Device Compatibility | Computer; PDU; Server |
| Country/Region | UK |
| INPUT | |
| Maximum Input Amps | 10.0 |
| Voltage Compatibility (VAC) | 250 |
| CONNECTIONS | |
| Side A - Connector 1 | BS1363 UK PLUG |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|--------------------------------------|-------------------------------|
| Side B - Connector 1 | IEC-320-C13 |
| PHYSICAL | |
| Plug Color | Black |
| Cable Jacket Material | PVC |
| Power Cord Jacket Type | H05VV-F |
| Cable Outer Diameter (OD) | 6.7 mm |
| Number of Conductors | 3 |
| Conductor Gauge | 24/0.20AS |
| Wire Gauge (AWG) | 18 |
| Wire Gauge (OD - mm ²) | 0.75 |
| Power Cord Color | Black |
| Cable Length (ft.) | 6.56 |
| Cable Length (m) | 2.00 |
| Cable Length (cm) | 100 |
| Shipping Dimensions (hwd / in.) | 9.02 x 7.01 x 0.50 |
| Shipping Dimensions (hwd / cm) | 22.91 x 17.81 x 1.27 |
| Shipping Weight (lbs.) | 0.49 |
| Shipping Weight (kg) | 0.22 |
| Unit Dimensions (hwd / in.) | 9.020 x 7.010 x 0.500 |
| Unit Packaging Type | Polybag |
| Unit Weight (lbs.) | 0.48 |
| Unit Weight (kg) | 0.22 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 5° to 158° F (-15° to 70° C) |
| Storage Temperature Range | 5° to 140° F (-15° to 60° C) |
| Operating Humidity Range | 20% TO 80% RH, NON-CONDENSING |
| Storage Humidity Range | 20% TO 80% RH, NON-CONDENSING |
| FEATURES & SPECIFICATIONS | |
| Antibacterial | No |
| Armored Cable | No |
| Angled Plug | No |
| High Voltage | Yes |
| Locking Plug | No |
| Coiled Power Cord | No |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|-------------------------------------|--------------------------------|
| Locking | No |
| STANDARDS & COMPLIANCE | |
| Product Compliance | CE (Europe); REACH; RoHS; UKCA |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.