

European Computer Power Cord, C7 to Schuko, 2.5A, 250V, 18 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: P059-006



C7 to Schuko EU power cord connects your notebook computer or laptop with a C8 power inlet to a Schuko outlet.

Features

European Computer Power Cord Connects Notebook Computers to a Schuko AC Outlet This C7 to Schuko power cord is designed for connecting a notebook computer, laptop or other device with a C8 inlet to a UPS system, PDU or other Schuko outlet. It is also a durable replacement for a worn-out or lost laptop power cord. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

Highlights

- EU power cable recommended for powering notebooks and laptops with C8 inlets
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for a worn-out or missing laptop adapter power cable

Applications

- Connect a laptop or notebook computer to a PDU up to 6 ft. (1.8 m) away in your workstation
- Extend an existing power connection up to 6 ft. (1.8 m) to more easily place a device or reach a power source
- Provide a high-quality replacement for a worn-out or missing laptop power cord

Package Includes

- P059-006 C7 to Schuko, European Computer Power Cord, 6 ft. (1.8 m), Black

Specifications

OVERVIEW	
UPC Code	037332205421
Country/Region	Europe
INPUT	
Maximum Input Amps	2.5
Cable Length (ft.)	6
Cable Length (m)	1.8



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (in.)	72
Voltage Compatibility (VAC)	250
PHYSICAL	
Color	Black
Number of Conductors	2
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	32.51 x 22.50 x 1.27
Shipping Dimensions (hwd / in.)	12.80 x 8.86 x 0.50
Shipping Weight (kg)	0.10
Shipping Weight (lbs.)	0.22
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	1.02
ENVIRONMENTAL	
Operating Temperature Range	41 to 95 F (5 to 35 C)
Storage Temperature Range	41 to 95 F (5 to 35 C)
Relative Humidity	0% to 65% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	CEE 7/16 SCHUKO PLUG
Side B - Connector 1	IEC-320-C7 (NON-POLARIZED)
SPECIAL FEATURES	
High Voltage	Yes
Locking Plug	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>