

UK Computer Power Cord - BS1363 to C5, 2.5A, 250V, 18 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: P060-006



UK computer power cord connects your computer or peripheral with a C6 inlet to any grounded AC power outlet that accepts BS1363 plugs.

Features

UK Plug to C5 Power Cord Connects Notebook Computers to a BS1363 AC Outlet This UK computer power cable is designed for connecting a notebook computer, laptop or other device with a three-slot C6 inlet to a UPS system, PDU or other BS1363 outlet. It is also a durable replacement for a worn-out or lost laptop power cord. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

Specifications

OVERVIEW	
UPC Code	037332153630
Device Compatibility	Laptop; Computer; UPS; PDU
Country/Region	UK
INPUT	
Maximum Input Amps	2
Voltage Compatibility (VAC)	100-250
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC

Highlights

- UK computer power cable for powering notebooks and laptops with C6 inlets
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for worn-out or missing UK IEC power cord

Applications

- Connect a laptop or notebook computer to a PDU up to 6 ft. (1.8 m) away in your workstation
- Extend an existing power connection up to 6 ft. (1.8 m) to more easily place a device or reach a power source
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P060-006 BS1363 to C5 UK Computer Power Cable, 6 ft. (1.8 m), Black

Cable Jacket Rating	H05VV-F
Power Cord Jacket Type	H05VV-F
Cable Outer Diameter (OD)	6.5mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.82
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	9.06 x 7.09 x 0.50
Shipping Dimensions (hwd / cm)	23.01 x 18.01 x 1.27
Shipping Weight (lbs.)	0.46
Shipping Weight (kg)	0.21
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
ENVIRONMENTAL	
Operating Temperature Range	-4 to 140 F (-20 to 60 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Operating Humidity Range	20% to 70% RH
Storage Humidity Range	20% to 80% RH
CONNECTIONS	
Side A - Connector 1	BS1363 UK PLUG
Side B - Connector 1	IEC-320-C5
FEATURES & SPECIFICATIONS	
High Voltage	Yes
Locking Plug	No
Antibacterial	No
Angled Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	UL Listed; cUL Listed
Product Compliance	CE (Europe); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.