

## VGA to HDMI Adapter Cable with Audio and USB Power (M/M), 1080p 60 Hz, 6 ft. (1.8 m)

MODEL NUMBER: P116-006-HDMI-A



All-in-one solution converts analog VGA video and 2-channel audio for display on an HDMI monitor, projector or TV without having to upgrade your source device.

### Features

#### Converts VGA Video + Audio to HDMI

- Recommended for home theaters, media presentations and digital signs
- Saves money by allowing you to use existing analog source equipment without any expensive upgrades
- Supports HD video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Gold-plated connectors and contacts for maximum conductivity and minimum data loss

#### Plug-and-Play Convenience

- Ready to use right from the box—no software or drivers required
- Connects easily to source's VGA, 3.5 mm audio and USB ports and display's HDMI port
- Bus-powered via USB connection—no external power supply required

## Specifications

OVERVIEW	
UPC Code	037332203342
Product Type	Passive Cable
Technology	HDMI; Stereo Audio; VGA/SVGA
Cable Type	Passive
VIDEO	
Max Supported Video Resolution	1920 x 1200 (1080p)

### Highlights

- Saves money by eliminating need to update expensive equipment
- Supports HD video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Bus-powered via USB connection
- Plug and play—no software or drivers to install

### System Requirements

- Source device with VGA, 3.5 mm and USB ports
- Display device with HDMI port

### Package Includes

- P116-006-HDMI-A VGA + Audio to HDMI Adapter Cable (M/M), 6 ft.
- Quick Start Guide

PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Unit Weight (lbs.)	0.3
Unit Weight (kg)	0.14
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Relative Humidity	10% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HD15 (MALE)
Side B - Connector 2	3.5MM (MALE)
Side B - Connector 3	USB A (MALE)
Latching or Gripping Connector	No
FEATURES & SPECIFICATIONS	
IP68 Rated	No
HDCP Specification	1.2
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty