

DVI to VGA Adapter Cable (DVI-I Dual-Link to HD15 M/F), 8 in. (20.3 cm)

MODEL NUMBER: P120-08N



Highlights

- Converts a DVI-I Dual Link signal to a VGA Female connection or VGA signal to a DVI-I Dual Link male connection
- Fully shielded and molded construction
- Supports computer video resolutions up to 1920 x 1200, and HD video resolutions up to 1920 x 1080 (1080p)

System Requirements

- DVI-I enabled computer (supports both Analog and Digital DVI) or VGA enabled computer

Package Includes

- 8-in. DVI-I Dual Link Male to VGA Female Adapter Cable

Features

- Connect a VGA monitor to your computer's DVI-I port or a DVI-I monitor to your computer's VGA port
- Double shielded and fully molded construction
- Supports computer video resolutions up to 1920 x 1200, and HD video resolutions up to 1920 x 1080 (1080p)

Specifications

OVERVIEW	
UPC Code	037332182517
Product Type	Passive Cable
Technology	DVI; VGA/SVGA
VIDEO	
Max Supported Video Resolution	1920 x 1200 (1080p)
CONNECTIONS	
Side A - Connector 1	DVI-I DUAL LINK (MALE)
Side B - Connector 1	HD15 (FEMALE)
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Jacket Rating	VW-1
Cable Length (ft.)	0.7
Cable Length (m)	0.21
Cable Length (in.)	8.4
Cable Length (cm)	20.32
Shipping Dimensions (hwd / in.)	0.25 x 0.50 x 9.00
Shipping Dimensions (hwd / cm)	0.64 x 1.27 x 22.86
Shipping Weight (lbs.)	0.10
Shipping Weight (kg)	0.05
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.