

DVI to VGA Adapter Cable (DVI-I Dual Link to HD15 M/F), 8-in. (20.32 cm)

MODEL NUMBER: P120-08N



Features

- Connect a VGA monitor to your computer's DVI-I port
- Double shielded and fully molded construction
- Supports computer video resolutions up to 1920 x 1200, and HD video resolutions up to 1920 x 1080 (1080p)

Specifications

OVERVIEW	
UPC Code	037332182517
Technology	DVI; VGA/SVGA
INPUT	
Cable Length (ft.)	0.7
Cable Length (m)	0.2
Cable Length (in.)	8
Cable Length (cm)	20.32
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	0.64 x 1.27 x 22.86
Shipping Dimensions (hwd / in.)	0.25 x 0.50 x 9.00

Highlights

- Converts a DVI-I Dual Link signal to a VGA Female connection
- Fully shielded and molded construction
- Supports computer video resolutions up to 1920 x 1200, and HD video resolutions up to 1920 x 1080 (1080p)

System Requirements

- DVI-I enabled computer (supports both Analog and Digital)

Package Includes

- 8-in. DVI-I Dual Link Male to VGA Female Adapter Cable



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.10
CONNECTIONS	
Side A - Connector 1	DVI-I DUAL LINK (MALE)
Side B - Connector 1	HD15 (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>