



4K HDMI Audio Extractor with TOSLINK, RCA and 3.5 mm Stereo Output, 7.1 Channel, 4K 60 Hz, HDR

MODEL NUMBER: P130-000-AUD4K6











Separates the audio track from an HDMI audio/video signal and sends it to a stereo receiver, speakers or other separate audio system. Ideal for connecting a Blu-ray player or other HDMI source to speakers with no HDMI input.

Description

The P130-000-AUD4K6 4K HDMI Audio Extractor connects an HDMI source, such as a Blu-ray player or desktop computer, to audio speakers that don't have an HDMI input port. Recommended for home or office workstations, digital signage, and classrooms, it can save you money by eliminating the need to upgrade to a new audio system or speakers.

The P130-000-AUD4K6 extracts the audio track from the HDMI signal and sends it directly to an alternate digital or analog non-HDMI audio device. To power the unit, connect the included USB Micro-B cable between the P130-000-AUD4K6 and a USB port on the HDMI source or a USB charger.

The compact HDMI audio de-embedder/extractor unit features 3.5 mm stereo, TOSLINK digital optical and RCA digital audio outputs to match most non-HDMI receivers and audio devices. It supports two-channel stereo and multi-channel audio up to 7.1 surround sound. It also supports uncompressed audio, such as LPCM, and compressed audio formats, including DTS and Dolby Digital. LEDs indicate when the unit is receiving power and transmitting an audio/video signal.

On the video side, the P130-000-AUD4K6 transmits UHD video resolutions up to 4K x 2K (3840 x 2160) at 60 Hz, as specified in HDMI 2.0. It supports 24-bit True Color (8 bits per channel) at 4K x 2K, 36-bit Deep Color (12 bits per channel) at 1080p and optional 3D formats up to 60 Hz. It complies with HDCP 2.2 specifications to conform to the latest equipment and encryption standards.

Features

Extracts Audio from an HDMI Signal and Sends It to a Separate Audio DeviceRecommended for connecting an HDMI source to speakers that don't have HDMI inputIdeal for home or office workstations, digital signage or classroom use3.5 mm stereo, TOSLINK and RCA audio outputs connect to analog or digital non-HDMI audio equipment (audio and HDMI cables sold separately)LEDs indicate the unit is receiving power or transmitting an audio/video signal

Versatile Audio OptionsSupports 2-channel stereo and multi-channel audio up to 7.1 surround soundSupports uncompressed audio, such as LPCMSupports compressed audio, such as DTS and Dolby Digital

Vibrant UHD VideoTransmits UHD video resolutions up to 4K x 2K (3840 x 2160) @ 60 Hz, as specified in HDMI 2.0Supports High Dynamic Range (HDR) for richer contrast and expanded color accuracySupports 24-bit True Color (8 bits per channel) at 4K x 2KSupports 36-bit Deep Color (12 bits per channel) at 1080pSupports optional 3D formats up to 60 MHz

Highlights

- Features 3.5 mm stereo, TOSLINK optical and RCA audio outputs
- Supports multi-channel audio, including LPCM, DTS and Dolby Digital
- Supports UHD resolutions up to 4K @ 60 Hz for crystal-clear video
- Supports High Dynamic Range (HDR) for richer contrast and expanded color accuracy

System Requirements

- Source device with HDMI output
- Audio device with 3.5 mm, TOSLINK or RCA audio input

Package Includes

- P130-000-AUD4K6 4K HDMI Audio Extractor
- USB Micro-B cable, 3 ft.
- Owner's manual





Simple Plug-and-Play OperationNo software or drivers requiredIncluded 3 ft. USB Micro-B cable connects to HDMI source or USB charger to power the unitComplies with HDCP 2.2 standardsCompact unit measures just 3 x 2.4 x 1 in. for easy integration with your A/V setup

Specifications

-	
OVERVIEW	
UPC Code	037332203434
Technology	HDMI; Stereo Audio; Toslink/SPDIF
VIDEO	
HDR Support	Yes
CONNECTIONS	
Side A - Connector 1	HDMI (FEMALE)
Side A - Connector 2	MICRO-USB B (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	TOSLINK (MALE)
Side B - Connector 3	3.5MM (FEMALE)
Side B - Connector 4	RCA (FEMALE)
PHYSICAL	
Color	Black
Cable Length (ft.)	0
Cable Length (m)	0.00
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.