

## 4K HDMI Audio De-Embedder/Extractor with TOSLINK, RCA and 3.5 mm Stereo Output, 5.1 Channel, HDCP, 4K 30Hz

MODEL NUMBER: P130-000-AUDIO



Separates the audio track from an HDMI audio/video signal and sends it to a stereo receiver, speakers or other separate audio system. Ideal for connecting a Blu-ray player or other HDMI source to speakers with no HDMI input.

### Description

The P130-000-AUDIO UHD 4K x 2K HDMI Audio De-Embedder/Extractor is an ideal solution for connecting an HDMI source, such as a Blu-ray™ player or video game system, to audio speakers that don't have an HDMI input port. It separates the audio track from the HDMI signal and sends it directly to an alternate HDMI audio system. It features 3.5 mm stereo, TOSLINK digital optical and RCA digital audio outputs to match most non-HDMI receivers and audio systems.

The P130-000-AUDIO supports both two-channel stereo and multi-channel audio up to 5.1 surround sound. It also supports both uncompressed audio, such as LPCM, and compressed audio formats, including DTS® and Dolby Digital®. An LED indicates when the unit is receiving power, transmitting an audio/video signal or transmitting 5.1-channel surround sound.

On the video side, the P130-000-AUDIO transmits Ultra High Definition (UHD) video resolutions up to 3840 x 2160 (4K x 2K) at 30 Hz. It supports 24-bit True Color (8 bits per channel) at 4K x 2K, 36-bit Deep Color (12 bits per channel) at 1080p, and optional 3D formats up to 50/60 Hz. Product is also HDCP compatible.

### Features

#### Extracts Audio from an HDMI Signal and Sends It to a Separate Audio System

- Ideal for connecting HDMI source to speakers that don't have HDMI input
- Features 3.5 mm stereo, TOSLINK digital optical and RCA digital audio outputs
- LED indicates the unit is receiving power or transmitting an audio/video signal
- Power Supply includes international plug adapters (North America, Europe, U.K and Australia)

#### Versatile Audio Options

- Supports 2-channel stereo
- Supports multi-channel audio up to 5.1 surround sound
- Supports uncompressed audio, such as LPCM
- Supports compressed audio, including DTS and Dolby Digital

### Highlights

- Supports multi-channel audio up to 5.1 surround sound
- Features 3.5 mm stereo, TOSLINK and RCA digital audio outputs
- Transmits UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 30 Hz
- Supports uncompressed audio, such as LPCM
- Supports compressed audio, including DTS and Dolby Digital

### Package Includes

- P130-000-AUDIO UHD 4K x 2K HDMI Audio De-Embedder/Extractor
- External power supply (Input: 100–240V, 50/60 Hz, 0.3A; Output: 5V, 1A)
- International plug adapters (North America, Europe, U.K. and Australia)
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

**Rich, Vibrant Ultra High Definition Video**

- Transmits UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 30 Hz
- Supports 24-bit True Color (8 bits per channel) at 4K
- Supports 36-bit Deep Color (12 bits per channel) at 1080p
- Supports optional 3D formats up to 50/60 Hz

## Specifications

OVERVIEW	
UPC Code	037332193193
Product Type	Video Adapter
Technology	HDMI; Stereo Audio; Toslink/SPDIF
CONNECTIONS	
Side A - Connector 1	HDMI (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	TOSLINK (MALE)
Side B - Connector 3	3.5MM (FEMALE)
Side B - Connector 4	RCA (FEMALE)
PHYSICAL	
Color	Black
Cable Length (ft.)	0
Cable Length (m)	0.00
FEATURES & SPECIFICATIONS	
HDCP Specification	1.3
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.