

4K HDMI to DisplayPort Active Adapter Video Converter with USB Power, HDMI to DisplayPort (M/F), 4K 30Hz, 6-in. (15.24 cm)

MODEL NUMBER: P130-06N-DP-V2



HDMI to DisplayPort adapter connects an HDMI audio/video source to a DisplayPort monitor. Also converts DVI and mini-DVI video signals using adapters (sold separately). Ideal for home theater, trade shows and classrooms.

Features

Sends HDMI Audio/Video Signals to a 4K DisplayPort Monitor or Projector

- Ideal for home theater setups, digital signage, trade show presentations and classroom lectures
- Male HDMI and female DisplayPort connectors
- Also connects DVI or mini-DVI source using adapter cables, such as P566-Series (sold separately)
- Built-in USB plug provides power if needed

Vibrant Audio/Video Quality

- Supports video resolutions up to 4096 x 2160 (4K x 2K) @ 30 Hz
- Supports 7.1-channel surround sound
- Transmits EDID info to ensure optimal display compatibility

Premium Construction for Top Signal Transfer

- Gold-plated connectors and contacts for maximum conductivity and minimum data loss
- Integral strain relief reduces stress and adds flexibility
- Compliant with HDCP 1.3 and DisplayPort 1.2a
- Fits easily into briefcase, backpack or laptop bag
- Plug-and-play—no software or drivers necessary

Specifications

OVERVIEW

Highlights

- Active converter works with all HDMI sources
- Supports video resolutions up to 4096 x 2160 (4K x 2K) @ 30 Hz
- Supports 7.1-channel surround sound
- Transmits EDID info to ensure optimal display compatibility
- Compliant with HDCP 1.3 and DisplayPort 1.2a

System Requirements

- Computer, Blu-ray player or other source with HDMI output
- Monitor or other display with DisplayPort input

Package Includes

- P130-06N-DP-V2 HDMI to DisplayPort Active Converter 4K (M/F)
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

UPC Code	037332200419
Product Type	Video Adapter
Technology	HDMI; DisplayPort
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (FEMALE); USB A (FEMALE)
Side B - Connector 1	HDMI (MALE)
PHYSICAL	
Color	Black
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6
Shipping Dimensions (hwd / in.)	0.85 x 3.90 x 4.70
Shipping Dimensions (hwd / cm)	2.16 x 9.91 x 11.94
Shipping Weight (lbs.)	0.18
Shipping Weight (kg)	0.08
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.