

DisplayPort to VGA Active Adapter – M/F, 1920 x 1200 (1080p), Black, 1 ft.

MODEL NUMBER: P134-001-VGA



DP to VGA converter connects a VGA monitor to the DisplayPort output on your laptop, PC or Chromebook.

Features

DP to VGA Converter Connects a DisplayPort Source to Your Existing VGA Display This DisplayPort to VGA active adapter connects a VGA monitor, projector or television to the DisplayPort output on your PC, Chromebook or other compatible computer or tablet. It features a male DP connector and a female HD15 connector, allowing you to continue using your existing VGA display and VGA cable to transmit video signals without the expense of a new DP display.

Transmits Outstanding 1080p Video for High-Definition Presentations Ideal for classrooms, lecture halls and anywhere else you may give a presentation, this DisplayPort to VGA converter supports computer video resolutions up to 1920 x 1200, including 1080p, and high-definition resolutions up to 1080p. The active adapter converts both Single-Mode and Dual-Mode (DP++) DisplayPort output. It's recommended for use with graphics cards, such as AMD Eyefinity, that do not output DP++ signals.

Ready to Use Right Out of the Package The plug-and-play adapter requires no software, drivers or external power, works with both Windows and Mac operating systems, and is compatible with laptops, tablets and other devices equipped with a female DisplayPort. With its small size, the P134-001-VGA is recommended for stowing in your laptop bag and carrying to school, the office or the latest trade show.

3-Year Warranty The P134-001-VGA is backed by a 3-year warranty, ensuring reliability and performance.

Highlights

- Continue using your current VGA display without the expense of a new DP monitor
- Delivers high-definition picture quality at resolutions up to 1920 x 1200, including 1080p
- Compact unit fits easily into briefcase or laptop bag for instant use anywhere
- Plug-and-play operation with no software required for easy, immediate installation
- Ideal for video presentations and watching movies in HD on a VGA display

Applications

- Display 1080p video on an existing VGA monitor without the expense of buying a new DisplayPort monitor
- Extend your laptop's display to a secondary VGA monitor
- Give a video presentation in a classroom, conference room or trade show booth

System Requirements

- Source device with DisplayPort output
- Display device with VGA input
- Not for use with MST hubs. For compatibility with MST hubs, use a DisplayPort 1.2-compliant adapter, such as P134-06N-VGA-V2.

Package Includes

- P134-001-VGA DisplayPort to



VGA Active Adapter – M/F,
1920 x 1200 (1080p), Black, 1 ft.

Specifications

OVERVIEW	
UPC Code	037332212870
INPUT	
Cable Length (ft.)	1
Cable Length (in.)	12
Cable Length (cm)	31
PHYSICAL	
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
Operating Humidity Range	10% TO 85% RH, Non-Condensing
Storage Humidity Range	5% TO 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	HD15 (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	VGA/SVGA; DisplayPort
CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

<https://www.tripplite.com/products/product-certification-agencies>