

DisplayPort to Mini DisplayPort Adapter Cable (M/F), 4K 60 Hz, 3 ft. (0.9 m)

MODEL NUMBER: P134-003-MDP



Connects a Mini DisplayPort (mDP) monitor to a computer with a DisplayPort output.

Features

Sends UHD DisplayPort Audio/Video to a Mini DisplayPort Monitor or an mDP Computer to a DisplayPort Monitor

- Connects a DisplayPort computer to an mDP monitor or an mDP computer to a DisplayPort monitor
- Recommended for displaying DisplayPort video on a large monitor or digital sign
- Allows you to continue using an existing mDP display, instead of buying a new monitor

Vibrant, Superior Video Quality

- Supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 60 Hz, including 1080p
- 3840 x 2160 (4K x 2K) @ 60 Hz video resolutions supported up to 10 ft. (Including P134 adapter cable)
- 3840 x 2160 (4K x 2K) @ 30 Hz video resolutions supported up to 16 ft. (Including P134 adapter cable)
- Works with both Single-Mode and Dual-Mode (DP++) DisplayPort graphics cards

Superior Materials for Superior Performance

- Gold-plated connectors and contacts for excellent conductivity
- Integral strain relief for long life
- Plug and play—no software or drivers required

Specifications

OVERVIEW	
UPC Code	037332198617
Product Type	Passive Cable
Technology	DisplayPort

Highlights

- Supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 60Hz
- Works with both Single-Mode and Dual-Mode graphics cards
- Gold-plated connectors and contacts
- Integral strain relief
- Plug and play—no software or drivers required

System Requirements

- Computer with a DisplayPort or Mini DisplayPort output
- Monitor with a Mini DisplayPort or DisplayPort input

Package Includes

- P134-003-MDP DisplayPort to Mini DisplayPort Cable Adapter (M/F), 3 ft.



PHYSICAL	
Color	White
Cable Jacket Color	White
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Cable Length (cm)	91.44
Shipping Dimensions (hwd / cm)	15.24 x 10.16 x 1.27
Shipping Dimensions (hwd / in.)	6.00 x 4.00 x 0.50
Shipping Weight (kg)	0.04
Shipping Weight (lbs.)	0.08
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	MINI DISPLAYPORT (FEMALE)
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>