

## DisplayPort to DVI Active Adapter Video Converter, DP ver 1.2, (M/F), 6-in. (15.24 cm)

MODEL NUMBER: P134-06N-DVI-V2



Converts a DisplayPort 1.2 video signal for display on a DVI monitor, projector or television.

### Features

#### Send High-Definition DisplayPort 1.2 Video Signals to a DVI Display

- Connects DisplayPort 1.2 computer to DVI-enabled monitor, projector or TV
- Ideal for displaying video on large monitor or digital sign
- Female DVI-I dual-link and male DisplayPort connectors
- Backward compatible with previous DisplayPort generations

#### Vibrant, Superior Video Quality

- Supports HD video resolutions up to 1920 x 1080 (1080p)
- Converts both Single-Mode and Dual-Mode DisplayPort output
- Works with graphics cards that don't output DP++ signals, such as AMD Eyefinity

#### Superior Materials for Superior Performance

- Gold-plated connectors and contacts for excellent conductivity
- Integral strain relief for long life
- Plug-and-play—no software, drivers or power supply necessary
- Fits easily into briefcase, backpack or laptop bag

## Specifications

OVERVIEW	
UPC Code	037332192035

### Highlights

- Active converter works with all DisplayPorts
- Supports HD video resolutions up to 1920 x 1080 (1080p)
- Converts both Single-Mode and Dual-Mode DisplayPort output
- Plug and play—no software, drivers or power supply needed
- Gold-plated connectors and contacts

### Package Includes

- P134-06N-DVI-V2 DisplayPort 1.2 to DVI Active Converter (M/F), 6 in.



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Technology	DVI; DisplayPort
<b>PHYSICAL</b>	
Color	Black
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Weight (kg)	0.04
Shipping Weight (lbs.)	0.09
<b>CONNECTIONS</b>	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	DVI-I DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>