

DisplayPort to DVI Active Adapter Video Converter, DP ver 1.2, (M/F), 6 in., 50 pack

MODEL NUMBER: P134-06NDVIV2BP



Active adapter connects a DVI display to the DisplayPort (DP) output on your laptop or desktop computer for playing 1080p video.

Features

DisplayPort 1.2 to DVI Converters Connect DP Source to DVI DisplayThis set includes 50 Tripp Lite P134-06N-DVI-V2 DisplayPort to DVI active adapters. Each adapter connects a DVI monitor, projector or television to the DisplayPort output on your PC, Mac, Chromebook, MacBook, Microsoft Surface or other compatible computer or tablet. They feature a male DP connector and a female DVI-I dual-link connector, allowing you to continue using your existing DVI display and DVI cable to transmit video signals without the expense of a new DP display.

Transmit Outstanding 1080p Video for High-Definition PresentationsIdeal for classrooms, lecture halls and anywhere else you may need to connect to a DVI monitor, these DisplayPort to DVI converters support high-definition video resolutions up to 1920 x 1080 (1080p). The active adapters convert both Single-Mode and Dual-Mode (DP++) DisplayPort output. They come recommended for use with graphics cards, such as AMD Eyefinity, that do not output DP++ signals.

Ready to Use Right Out of the PackageThe plug-and-play DP to DVI adapters require no software, drivers or external power, work with both Windows and Mac operating systems, and are compatible with laptops, tablets and other devices equipped with a female DisplayPort. With its small size and built-in cable, the P134-06N-DVI-V2 is recommended for stowing in your laptop bag and carrying to school or the office.

Highlights

- 50-piece bulk pack of P134-06N-DVI-V2 DisplayPort to DVI video adapters
- Delivers high-definition picture quality at resolutions up to 1920 x 1080 (1080p)
- Active adapter converts Single- and Dual-Mode DP++ output for viewing on VGA display
- Compact unit fits easily into briefcase or laptop bag for instant use anywhere
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect your newer laptop to an older DVI monitor in a lecture hall or conference room for a video presentation
- Add a secondary monitor to the PC or laptop in your office or home workspace
- Display menus, ads, promos, directions and other digital signage applications

System Requirements

- Source device with DisplayPort output
- Display device with DVI input

Package Includes

- (50) P134-06N-DVI-V2 DisplayPort 1.2 to DVI Active Converters (M/F), 6 in.



Specifications

| OVERVIEW | |
|---------------------------------|---|
| UPC Code | 037332237705 |
| Technology | DVI; DisplayPort |
| INPUT | |
| Product Length (in.) | 5.9 |
| Product Length (ft.) | 0.49 |
| PHYSICAL | |
| Cable Jacket Type | VW-1 |
| Cable Outer Diameter (OD) | 4.5mm |
| Color | Black |
| Ferrite Core | No |
| Material of Construction | ABS, PVC |
| Shipping Dimensions (hwd / in.) | 4.10 x 15.75 x 17.75 |
| Shipping Weight (kg) | 2.09 |
| Unit Dimensions (hwd / in.) | 1.69 x 1.77 x 0.57 |
| Unit Weight (kg) | 0.10 |
| Unit Weight (lbs.) | 0.22 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32 to 113 F (0 to 45 C) |
| Storage Temperature Range | 14 to 176 F (-10 to 80 C) |
| Operating Humidity Range | 10% to 85% RH, Non-Condensing |
| Storage Humidity Range | 5% to 90% RH, Non-Condensing |
| CONNECTIONS | |
| Side A - Connector 1 | DISPLAYPORT (MALE) |
| Side B - Connector 1 | DVI-I DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK) |
| Connector Plating | Gold; Nickel |
| Contact Plating | Gold; Nickel |
| FEATURES & SPECIFICATIONS | |
| Max Supported Video Resolution | 1920 x 1080 @ 60Hz |
| Displayport Specification | 1.2 |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|-------------------------------------|--------------------------------|
| Driver Required | No |
| STANDARDS & COMPLIANCE | |
| Certifications | Tested to CE, FCC, RoHS, REACH |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>